




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECN-25-339919	25AUG2025	MK	MS

- 1



MOLDED PARTS: UL RATED 94V-0 THERMOPLASTIC, BLACK.
- 2

CONTACTS: PHOSPHOR BRONZE PER QQ-B-750.
- 3


CONTACTS: PLATED WITH .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000030 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMENATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- 4

POLARIZING FEATURE DOES NOT EXIST ON END OPPOSITE THE POSN #1 INDICATOR ON 10 POSN PRODUCT.
- 5

OBSOLETE



5	2.100	2.380	2.150	43	44	1-1658624-3
	3.100	3.380	3.150	63	64	1-1658624-2
	2.400	2.680	2.450	49	50	1-1658624-0
5	1.900	2.180	1.950	39	40	1658624-9
	1.600	1.880	1.650	33	34	1658624-8
	1.400	1.680	1.450	29	30	1658624-7
	1.200	1.480	1.250	25	26	1658624-6
	1.100	1.380	1.150	23	24	1658624-5
	.900	1.180	.950	19	20	1658624-4
	.700	.980	.750	15	16	1658624-3
	.600	.880	.650	13	14	1658624-2
	.400	.680	.450	9	10	1658624-1
D		C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. SAMICK 25AUG03		 TE Connectivity								
DIMENSIONS: INCHES			CHK C. ROHDE 25AUG03										
			APVD M. WALMSLEY 25AUG03		NAME RECEPTACLE ASSY, DUAL BAR POLARIZATION, LEAD FREE, AMP-LATCH™ NOVO								
			PRODUCT SPEC 108-40000										
			APPLICATION SPEC 114-40005										
			WEIGHT 0.000000										
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± ±			SIZE A2		CAGE CODE 00779		DRAWING NO C=1658624		RESTRICTED TO —				
MATERIAL SEE NOTES			FINISH SEE NOTES		CUSTOMER DRAWING			SCALE 4:1		SHEET 1 of 1		REV C1	