



- NOTES:
1. PRODUCT SPECIFICATION: 108-19041
 2. PACKAGING: ON PLASTIC TUBES, BOXED

BOARD TO BOARD CONTACT POST FOR 0.8min DIA HOLE

CONTACT: 0.4µm MIN SELECTIVE GOLD PLTD ON MATING CONTACT AREA AND 3.0µm MIN TIN PLTD ON CONTACT POST, OVER 1.25µm MIN NI PLTD UNDERLAYER

HOUSING: THERMOPLASTIC POLYESTER 20% GF, UL94-v0 COLOUR GREEN CONTACT: PH. BRONZE HO6

1-166089-5

CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED

tyco Electronics tyco Electronics AMP Italia S.p.A. C.so F.lli Cervi, 15 - Collegno (TO)

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION JULY 1986

© COPYRIGHT 1986 BY AMP-HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

H2	ET00-0047-04	D.C.	C.T.	05MAR2004
H1	ET00-0115-03	D.C.	C.T.	04JUL2003
H	ET00-0068-03	P.B	D.C	8-5-03
G	-	-	-	12-6-89
LTR.	REVISION RECORD	DR.	CHK.	DATE

C. SOUSA	DATE 08-07-86	WIRE RANGE	NAME	15 POS. AMP-EDGE CONN. , DUAL LOADED WITH B. T. B. CONTACTS
CHK. J. BROEKSTEEG	DATE 08-07-86	INSUL. RANGE		
APP. L. V. SOEST	DATE 09-07-86	SIZE A3	SHEET 1 OF 1	DRAWING NO C-166089
				REV. LTR. H2