



DO NOT SCALE
DIMENSIONS IN mm

METRIC

THIRD ANGLE
PROJECTION



NOTES:

- 1 1,25 μm SELECTIVE Au OVER 1,25 μm NI. REMAINDER 1,25 μm NI.
- 2 0,75 μm SELECTIVE Au OVER 1,25 μm NI. REMAINDER 1,25 μm NI.
- 3 0,4 μm SELECTIVE Au OVER 1,25 μm NI. REMAINDER 1,25 μm NI.
- 4 WIRE RANGE 0,5–1,5 mm², INSULATION RANGE 2,0–2,5 mm.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBS	—166636—5	SEE NOTE 3	BRASS	166479—7—
OBS	—166636—4	SEE NOTE 2	BRASS	166479—6—
OBS	—166636—3	SEE NOTE 1	PHOSPHORBRONZE	166479—5—
OBS	—166636—2	SEE NOTE 2	PHOSPHORBRONZE	166479—4—
OBS	—166636—1	SEE NOTE 1	BRASS	166479—2—

LOOSE PIECE		FINISH			MATERIAL	PARTNUMBER		
—	—	—	—	—	CUSTOMER DRAWING FOR REFERENCE ONLY WILL NOT BE UPDATED			
—	—	—	—	—	© COPYRIGHT 19 — BY AMP HOLLAND B.V. ALL INTERNATIONAL RIGHTS RESERVED.AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN AND/OR PATENTS PENDING.			
—	—	—	—	—	THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION _____,19____			
E2	ECR—25—237922	MK	AK	17MARCH25	AMP AMP HOLLAND B.V. 's—Hertogenbosch, The Netherlands.			
E1	ECO—09—024717	KK	AEG	28DEC09				
E	SR10—0506—02	F.B.	F.B.	17—01—03				
C	EH—1280—95	J.G.	R.v.L	26—10—95				
LTR.	REVISION RECORD	DR.	CHK.	DATE	NAME CRIMP—ON / SNAP—IN TAB RECEPTACLE STRIP			
DR.: J.Gibbels		CHK.: R.v.Lokven		APP.: —	DWG.No.	REV.LTR.	SHEET	A3
DATE: 26—10—95		DATE: —		DATE: —	C— 166479	E1	1 OF 1	