




THIS DRAWING IS A CONTROLLED DOCUMENT FOR TICO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		0-1703410-1		A	10POS.REC.HSG.		PA66-GF15		4,95		BLACK SIMILAR RAL9011		1						
		PART NO		REV	DESCRIPTION		VOLUME [mm³]		WEIGHT [g]		COLOUR		ITEM NO						
DIMENSIONS: (mm) 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ± 4 PLC ± ANGLES ±1°		DWN 06FEB2007		tyco Electronics		tyco Electronics AMP GmbH 64625 Bensheim (Germany)											
				CHK 06FEB2007															
				APVD 07FEB2007		NAME		10POS INLINER REC.HOUSING 8 x MCON1,2 AND 2 x AMP2,8 -											
				PRODUCT SPEC		-													
				APPLICATION SPEC											-				
MATERIAL		FINISH		WEIGHT		-		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO					
-		-		-		-		A2		00779		C-1703410		-					
-		-		-		CUSTOMER DRAWING		SCALE		2:1		SHEET		1 OF 1		REV		A1	