



注:  
 1. 最大電線束線径: φ15.5  
 最小電線束線径: φ10

類似 NO. 200517-2.

単位: 耗 DIMENSIONS IN MM. DO NOT SCALE PRINT

デイトコード

REV.	DESCRIPTION	DR.	CHK.	DATE
C	REVISED	SA	NO	9/97
B	REVISED (REV. C)	SA	NO	10/97
A	REVISED (REV. B)	SA	NO	8/97
D	RELEASED (REV. 0)	SA	NO	8/97
LTR.	変更 (REVISION RECORD)	DR.	CHK.	DATE

番号 (NUMBER)	名称 (NAME)	摘要 (REMARKS)	ITEM NO.
C-171032	34極180°ショートシールド	参考図面 (CUSTOMER COPY) REFERENCE ONLY	
組立部品 (REQUIRED PER ASSEMBLY)		©19__ BY AMP (Japan), Ltd. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING	
材料 (MATERIAL)	上参照	絶縁電線断面積 (WIRE RANGE)	mm <sup>2</sup> (AWG)
仕上 (FINISH)	上参照	被覆外径 (INSULATION DIA.)	mm (IN)
DR.	S. Yoshida 8/30/97	一般公差 (TOLERANCE)	±0.4
CHK.	S. Yoshida 8/30/97	EXCEPT (AS NOTED)	±1.0
DE.		尺度 (SCALE)	J B
APP.		名称 (NAME)	番号 (NO)
			C-171032 C