



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DM	APVD
A1		LC20-0056-12 / ECO-12-010512	28MAY2012	DM	BJ
B		LC20-0031-16 / ECO-16-005675	14APR2016	DM	BJ
C		LC20-0085-16 / ECO-16-011010	21JUL2016	DM	BJ
C1		LC20-0020-17 / ECO-17-001984	21FEB2017	DM	BJ
D		LC20-0060-19 / ECO-19-010173	29JUN2019	DM	BJ
E		LC20-0114-19 / ECO-19-016005	05NOV2019	DM	BJ



#2 (6/1) 1/0 (6/1) 2/0 (6/1)	#2 1/0 2/0	X-SMALL	1-83843-4	1-1710737-0
1/0 (6/1) 2/0 (6/1)	1/0 2/0	X-SMALL	1-83843-0	1710737-9
795 (24/7) (26/7), (30/7) (30/19), (54/7)	954	X-LARGE	1-83843-1	1710737-8
605 (30/19) 636 (26/7) (24/7), (30/19) 666.6 (24/7) (26/7)	715.5, 750, 795	X-LARGE	83843-6	1710737-7
477.0 (30/7) 556.5 (24/7) (26/7), (30/7) 605 (24/7) (26/7) 636 (18/1) (36/1)	600, 636, 650, 700	X-LARGE	83843-5	1710737-6
477.0 (26/7) 556.5 (18/1)	556.5	LARGE	83843-4	1710737-5
397.5 (18/1) (24/7), (26/7) (30/7) 477.0 (18/1)	450, 477, 500	LARGE	83843-3	1710737-4
266.8 (26/7) 336.4 (18/1) (26/7), (30/7)	397.5 336.4, 350	SMALL	83843-2	1710737-3
266.8 (18/1)	266.8	SMALL	83843-1	1710737-2
3/0 (6/1) 4/0 (6/1)	4/0	SMALL	83843-7	1710737-1
ACSR	AAC	YOKE SIZE IN ILD ASSEMBLY	REPLACEMENT TAP P/N	PART NO.

40,000 AMPERE RMS, ASYMMETRICAL	25,000 AMPERE RMS, SYMMETRICAL	900 AMPERE RMS	60 HERTZ	350 kV	69 kV AC
MOMENTARY CURRENT	THREE SECOND CURRENT	CONTINUOUS CURRENT ALLOWABLE RATING: (PER ANSI C37-32.3.2.1 2002)	FREQUENCY	BASIC IMPULSE INSULATION LEVEL (BIL)	VOLTAGE
RATINGS					

1. BODY STRENGTH: 10,000 lbs.
PULLING EYE STRENGTH: 6000 lbs.
2. FOR INLINE DISCONNECT SWITCH ASSEMBLY W/O TAPS,
REFER TO 1710736-X SERIES PART NUMBERS.
3. BLADE DETAIL MAY NOT BE EXACTLY AS SHOWN.
4. 1710737-9 WILL BE REPLACED BY 1-1710737-0
IN THE FUTURE.

THIS DRAWING IS A CONTROLLED DOCUMENT. DWG: D. MURUGIAH 12FEB2010
CHK: S. KAMEL 29MAR2010
APPV: B. JOHNSON 29MAR2010

TE TE Connectivity

NAME: INLINE DISCONNECT SWITCH ASSEMBLY WITH TAPS, AMPACT, 69 kV, 900 Amp

PRODUCT SPEC: -
APPLICATION SPEC: -

SIZE: A2 CAGE CODE: 00779 DRAWING NO: 1710737 RESTRICTED TO: -
WEIGHT: 0

CUSTOMER DRAWING SCALE: NTS SHEET: 1 of 1 REV: E