


Technical drawing of a U-shaped part. The drawing shows a cross-section of the part with the following dimensions:

- Top width: 3.6 ± 0.3
- Height: 3.8
- Bottom width: 8.5 ± 0.4
- Radius of the bottom curve: $R0.85 \pm 0.2$


The part is shown with a dashed line indicating the center of the bottom curve. The bottom curve is shaded with diagonal lines.

Technical drawing of a U-shaped part with the following dimensions:

- Height: (5.1)
- Top width: 4.9 ± 0.3
- Base width: $11.6^{+0.4}$
- Internal radius: $R1.3 \pm 0.2$



| | | | | | | | |
|--|-----------------------------|------|------|----------|-------------|--------------------------------|---------|
| - | - | - | - | - | - | - | - |
| - | - | - | - | - | - | - | - |
| - | - | - | - | - | - | - | - |
| 0-1718189-1 | 0-1718188-1 | A | - | CuNiSi | vorverzinnt | HD - Kontakt, 4mm ohne Rastung | - |
| Tyco Electronics PART NO. LOOSE PIECE | Tyco Electronics PART NO | REV. | PCS. | MATERIAL | SURFACE | DESCRIPTION | ITEM NO |
| | | | | | COLOR | | |

| | | | | | | | | | | | | | |
|--|--|--|--|---|--|---|--|--------------------|--|---|--|--------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT FOR AN INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESSES ZEICHNUNGSDOKUMENT WIRD DURCH AM INCORPORATED KONTROLLIERT. ÄNDERUNGEN, DIE DEN TECHNISCHEN FORTSCHRITT BEZÜGLICH, SIND VORGEHTEN. BEN JEDELS SETZTGEHTIGEN ÄNDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE. | | DWN R. Schaefer CHK - | | 08-OCT-03 - | | AMP tyco Electronics AMP GmbH D - 64625 Bensheim | | | | | | | |
| DIMENSIONS: DIMENSIONS: mm  | | TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN n. ISO 8015 n. ISO 2768 - mH - E n. DIN 16901 - 140 0 1 PL C ± 2 PL C ± 3 PL C ± ANGLES/WINKEL ± | | APVD - PRODUCT SPEC PRODUKTSPEZ. 108-18962 APPLICATION SPEC VERARBEITUNGSSPEZ. 114-18668 | | NAME SOCKET, DIA4mm, HIGH-PRESSURE WITHOUT SNAP Buchse, ø4mm, Hochdruckkontakt ohne Rastung | | | | | | | |
| MATERIAL CuNiSi, X10CrNi18 8 | | FINISH/OBERFLÄCHE/FARBE - | | WEIGHT GEWICHT 1g | | SIZE A2 | | GAGE CODE 00779 | | DRAWING NO ZEICHNUNGS-NR. C-1718188 | | RESTRICTED TO NUR FUER - | |
| CUSTOMER DRAWING | | | | /KUNDENZEICHNUNG | | | | MASSSTAB 10:1 | | BLATT 1 VON 1 | | REV A2 | |