








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B3	REVISED PER ECR-23-178763	04JUL2023	SM	WZ








- HOUSING AND TINE PLATE: LCP, 94V-0, BLACK.
CONTACT: PHOSPHOR BRONZE.
RETENTION LEG: BRASS.
- CONTACT: GOLD FLASH OVER 0.76 μ m MIN PALLADIUM-NICKEL, OR 0.76 μ m MIN GOLD PLATING FOR A LENGTH OF 2.00 MIN FOR A LENGTH OF 1.00 MAX FROM MATING END, 3.75 μ m MATTE - TIN FOR A LENGTH OF 3.40 MIN FROM OPPOSITE END, BOTH OVER 1.27 μ m MIN NICKEL.
RETENTION LEG: 3.81 μ m MIN TIN-CU OVER 1.27 μ m MIN NICKEL.
- G, J AND H INDICATE NUMBER OF POSITION MARKED ON ASSEMBLY. SEE TABLE.
- CONNECTOR WILL ACCOMMODATE PRINTED CIRCUIT BOARD THICKNESS OF 0.80 TO 1.60.
- ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.

B1	OBSOLETE	120	61	60	86.13	82.33	83.27	120	1734359-3
		100	51	50	73.43	69.63	70.57	100	1734359-2
B1	OBSOLETE	80	41	40	60.73	56.93	57.87	80	1734359-1
		J	H	G	C	B	A	POS.	PART NUMBER




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN O. HU 07FEB2006		TE Connectivity Ltd.											
DIMENSIONS: mm		CHK S. HOU 07FEB2006													
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - 		APVD W.J. KE 07FEB2006	NAME PLUG ASSEMBLY, RIGHT ANGLE, BOARD-TO-BOARD, CHAMP .050, SERIES I -											
			PRODUCT SPEC 108-57876												
			MATERIAL SEE NOTE		FINISH SEE NOTE		APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO		RESTRICTED TO	
							-		A3		00779	C-1734359		-	
CUSTOMER DRAWING				WEIGHT -		SCALE -		SHEET 1 OF 3		REV B3					

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



⑥	OBSOLETE	5.83	3.40	21	16	336	1734359-3	120
		4.95	2.63	21	16	336	1734359-2	100
⑥	OBSOLETE	3.91	2.12	21	16	336	1734359-1	80
		G.W./CARTON (KG)	N.W./CARTON (KG)	PCS/TUBE	TUBES/CARTON	QUANTITY/CARTON (PCS)	PART NUMBER	POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity Ltd.					
		CHK						
		APVD						
		PRODUCT SPEC						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME				
		0 PLC ± -		PLUG ASSEMBLY, RIGHT ANGLE, BOARD-TO-BOARD, CHAMP .050, SERIES I				
		1 PLC ± -						
		2 PLC ± -						
		3 PLC ± -						
		4 PLC ± -						
		ANGLES ± -						
		FINISH						
MATERIAL				APPLICATION SPEC		SIZE		
				WEIGHT		CAGE CODE		
				CUSTOMER DRAWING		DRAWING NO		
						RESTRICTED TO		
						SCALE		
						SHEET		
						REV		