







LOC DY	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-




RECOMMENDED FFC/FPC



RECOMMENDED PCB LAYOUT (THK= 1.6±0.1)
(FOR EVEN POSITION CONNECTORS)
NON-ACCUMULATIVE TOLERANCE



RECOMMENDED PCB LAYOUT (THK= 1.6±0.1)
(FOR ODD POSITION CONNECTORS)
NON-ACCUMULATIVE TOLERANCE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WYLEE	15JUN04		TE Connectivity															
DIMENSIONS: mm		CHK V TAN	29MAR2013		NAME ASSY, 1.00mm FFC CONN TYPE 2, DIP, H, AU-PLATED -															
		APVD SE LEONG	29MAR2013																	
MATERIAL 	TOLERANCES UNLESS OTHERWISE SPECIFIED: <table><tr><td>0 PLC</td><td>±0.30</td></tr><tr><td>1 PLC</td><td>±0.30</td></tr><tr><td>2 PLC</td><td>±0.30</td></tr><tr><td>3 PLC</td><td>±-</td></tr><tr><td>4 PLC</td><td>±-</td></tr><tr><td>ANGLES</td><td>±3°</td></tr></table>	0 PLC	±0.30	1 PLC					±0.30	2 PLC	±0.30	3 PLC	±-	4 PLC	±-	ANGLES	±3°	PRODUCT SPEC 108-51069		
		0 PLC	±0.30																	
1 PLC	±0.30																			
2 PLC	±0.30																			
3 PLC	±-																			
4 PLC	±-																			
ANGLES	±3°																			
		APPLICATION SPEC -			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO												
		WEIGHT -			A300779		C-1735245		-											
CUSTOMER DRAWING					SCALE	5:1		SHEET	2 OF 2	REV	B2									