





LOC		DIST		REVISIONS					
DY		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED FOR PRODUCTION			07MAR2016	TX	SH
			A1	REVISED AS PER ECN-24-284280			13SEP2024	NR	ZW

NOTES:


- 1 MATERIAL:
HOUSING: HIGH TEMP THERMOPLASTIC, UL94V-0,
COLOR:BLACK
CONTACT: COPPER ALLOY
BOARDLOCK: COPPER ALLOY
- 2 FINISH:
CONTACT AREA: MIN 0.76µm GOLD PLATING
SOLDERTAIL: MIN 2.54µm MATTE TIN PLATING
UNDERPLATE: MIN 1.27µm NICKEL PLATING
- 3 PIN #P4 AND #P12 ONLY
- 4 SOLDERTAIL TO BE 0.05 MAX ABOVE
AND 0.10 MAX BELOW DATUM E
- 5 1.33 MAX MEASURED AT DATUM C



DETAIL A
SCALE 8:1

TRAY	YES	1735961-3
TAPE & REEL	YES	1735961-2
TRAY	NO	1735961-1
PACKAGING	PICK-UP CAP 1	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YM LEE	8DEC11	 TE Connectivity			
DIMENSIONS: mm		CHK SF LEONG	8DEC11				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD SF LEONG	8DEC11	NAME 12G SAS/PCIe COMBO RECEPTACLE (WITH TH BOARDLOCK) 15P+6P+7P+40P			
0 PLC ± 1 PLC ±0.20 2 PLC ±0.20 3 PLC ±0.20 4 PLC ± ANGLES ±3° FINISH		PRODUCT SPEC 108-51109 APPLICATION SPEC 114-60017 WEIGHT -		SIZE A200779	CAGE CODE C-1735961	DRAWING NO -	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 2:1		SHEET 1 OF 2		REV A1	

A1471-9 (3/11)