

LOC	DIST	REVISIONS				
DF	00	P	LTR	DESCRIPTION	DATE	APVD
			1	CONVERTED RADAILL DWG TO TYCO ACAD DWG	11/03	—
			2	REVISED	22APR10	RF JM


- 1

FRONT AND REAR INSULATORS: THERMOSET EPOXY PER ASTM D 5948
CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194
- 2




DATE CODE: YEAR & WEEK (YYWW)
- 3

DESCRIPTIVE PART NUMBER: GPRAN17PA
THIS INSERT CONTAINS 12 CAVITIES FOR SIZE 22 PIN CONTACTS
THIS INSERT CONTAINS 5 CAVITIES FOR SIZE 20 PIN CONTACTS
- 4

THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL SA.






MATING FACE



THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

1738077-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG NOV03		 Tyco Electronics Corporation Harrisburg, PA 17105-3608				
DIMENSIONS: mm [INCHES]		CHK J MOSIER NOV03						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J MOSIER NOV03		NAME GPR-A PIN INSERT, CLASS N, CONTACT ARRANGEMENT 17			
	0 PLC ± -		PRODUCT SPEC —					
	1 PLC ± -		APPLICATION SPEC —					
	2 PLC ± 0.05 [.002]		—					
	3 PLC ± -		WEIGHT —		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	4 PLC ± -		—		A2	00779	C=1738077	—
	ANGLES ± -		—					
	FINISH —		—					
MATERIAL		CUSTOMER DRAWING		SCALE 1:1		SHEET 1 of 1		REV 2