


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	00		O	CONVERTED RADIAL DWG TO TYCO ACAD DWG	04/04	—	—
			1	REVISED	22APR10	RF	JM

1 FRONT & REAR INSULATORS: THERMOSET EPOXY PER ASTM D5948
CONTACT RETENTION CLIPS: COPPER ALLOY PER ASTM B194
REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988B, EXCEPT 4.6.6.1




2 DATE CODE: YEAR & WEEK (YY WW)

3. DESCRIPTIVE PART NUMBER: GPRBE20C1SB
THIS INSERT CONTAINS:
19 CAVITIES FOR SIZE 20 SOCKET CONTACTS
1 CAVITY FOR SIZE 5 SOCKET CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS
UNDER A LICENSE FROM RADIAL SA.



MATING FACE



THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

1738144-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R FLAIG	NOV03	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK J MOSIER	NOV03				
		APVD J MOSIER	NOV03	NAME GPR-B SOCKET INSERT CLASS E CONTACT ARRANGEMENT 20C1 KEY B			
		PRODUCT SPEC		SIZE A2	CAGE CODE 00779	DRAWING NO C=1738144	RESTRICTED TO —
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SCALE 1:1			
MATERIAL		WEIGHT		SHEET 1 OF 1			
FINISH		CUSTOMER DRAWING		REV 1			