





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
-	-		I	REDRAWN IN PRO/E	04MAY2010	RF JM



MATING FACE



1 FRONT & REAR INSULATOR: HIGH-TEMP THERMOPLASTIC OR THERMOSET EPOXY PER ASTM D5948.
CONTACT RETENTION CLIPS: STAINLESS STEEL PER AISI 302 OR COPPER ALLOY PER ASTM B194
REAR GROMMET: FLUOROSILICONE ELASTOMER PER MIL-R-25988 B, EXCEPT 4.6.6.1

2 DATE CODE: YEAR & WEEK (YY WW)

3. DESCRIPTIVE PART NUMBER GPRBH28PB
THIS INSERT CONTAINS: 22 CAVITIES FOR SIZE 22 PIN CONTACTS
AND 6 CAVITIES FOR SIZE 15 OR 16 PIN CONTACTS.

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS UNDER A LICENSE FROM RADIAL L SA.

THIS PRINT IS
PRELIMINARY
UNQUALIFIED PRODUCT
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

1738162-1
PART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN BH	04MAY10	Tyco Electronics Harrisburg, PA 17105-3608		
		CHK JPM	04MAY10			
		APVD JPM	04MAY10	NAME INSERT ASSEMBLY, PIN, CLASS H - WITH REAR GROMMET ARRANGEMENT 28, KEY B, GPRB		
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	SIZE	CAGE CODE
		0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ±1 FINISH		APPLICATION SPEC	DRAWING NO	RESTRICTED TO
MATERIAL 1 -				WEIGHT -	A200779	C-1738162
				CUSTOMER DRAWING	SCALE 3:1	SHEET OF REV