

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
0		CONVERTED RADIALL DWG TO TYCO ACAD DWG	11/03	--	--		
1		REVISED	22APR10	RF	JM		

1 INSERT : THERMOSETTING FIBERGLASS FILLED PER ASTND-5948-96  
 WITH METALLIC RETENTION CLIPS PER ASTH-B-194  
 REAR GROMMET : FLUOROSILICONE ELASTOMER PER MIL-R-25988 B EXCEPT 4.6.6.1




2 DATE CODE: YEAR & WEEK (YY WW)

3. DESCRIPTIVE PART NUMBER: GPRBH34PA  
 THIS INSERT CONTAINS:  
 18 CAVITIES FOR SIZE 22 PIN CONTACTS  
 16 CAVITIES FOR SIZE 20 PIN CONTACTS

4. THIS PRODUCT IS SOLD BY TYCO ELECTRONICS  
 UNDER A LICENSE FROM RADIALL SA.



MATING FACE



THIS PRINT IS  
**PRELIMINARY**  
 UNQUALIFIED PRODUCT  
 CONTACT PRODUCT ENGINEERING  
 BEFORE USING THIS PRINT

1738177-1  
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	NOV03	Tyco Electronics Corporation	
DIMENSIONS: mm [INCHES]		R FLAIG	NOV03	Harrisburg, PA 17105-3608	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	NOV03	NAME	
0 PLC ± -		J MOSIER	NOV03	GPR-B PIN INSERT	
1 PLC ± -		APVD	NOV03	CLASS H	
2 PLC ± 0.05 [.002]		J MOSIER	NOV03	CONTACT ARRANGEMENT 34 KEY A	
3 PLC ± -		PRODUCT SPEC		SIZE	RESTRICTED TO
4 PLC ± -		APPLICATION SPEC		A2	
ANGLES ± -		WEIGHT		CAGE CODE	DRAWING NO
FINISH				00779	C=1738177
MATERIAL		CUSTOMER DRAWING		SCALE	SHEET
1				1:1	1 of 1
				REV	1