









LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
				RELEASED (FC00-0186-04)	13/SEP/'04	YD.
			A	REVISED (FC00-0030-05)	25/JAN/'05	YD.




3D - VIEW



- NOTE.
1. PULL-OUT FORCE OF THE CONTACT : Min 25N WHEN V = 25mm/min.
 2. BE MATED WITH PLUG HSG (P/N : 965444-1) SMOOTHLY.

NO	DESCRIPTION	PART NO.	MATERIAL	COLOR/FINISH	Q'TY
2	063 SQUARE CONTACT PIN FOR HLLD	0-368314-1	PHOSPHOR BRONZE	TIN	3
1	MQS. PIN HEADER, 3Pos.	0-1743157-2	PBT GF 15	BLACK	1
	MQS. PIN HEADER, 3Pos.	0-1743157-1	PBT GF 15	NATURAL	1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN : YD. LEE		NAME				
DIMENSIONS: mm		CHK : BM JANG						
 3rd ANGLE PROJECTION		APVD : CS LEE						
		PRODUCT SPEC ----						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC ----		MQS, PIN HEADER ASS'Y 3Pos.(V-TYPE)				
DECIMALS : ± 0.3 ANGLES : ± 3°		WEIGHT ----						
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
SEE TABLE		SEE TABLE		A3	00779	C= 1743156		
						SCALE 3 : 1	SHEET 1 OF 1	REV A