


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION







COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
DS	-		A	RELEASED		20/DEC/'05	JK



SECTION A-A




(SCALE 1:1)

NOTES:


1. GENERAL TOLERANCE IS ± 0.3
2. CONDITION OF DELIVERY :
DBL IN 1ST. LOCKING POSITION
LEVER HSG IN 2ND. LOCKING POSITION
3. APPLIED PLUG ASS'Y P/N: X-1743528-X
4. APPLIED REC. CONTACT P/N : TABLE 1
5. CHECK CONVERSION KEY CODE

TABLE 1			
TYPE	Part NO.	WIRE SIZE(mm ²)	MATERIAL/FINISH
.040	0-316836-1	0.3 - 0.85	CuNiSi ALLOY / PRE-TIN
	1-368085-1	0.3 - 0.5	CuNiSi ALLOY / 0--PRE-TIN / 1--GOLD
.090	0-368084-1	0.85 - 1.25	
	1-368084-1		
	0-368083-1	2.0	
	1-368083-1		



SHAPE OF CONVERSION TYPE(TABLE 1.)	
0-1743531-1(NATURAL)	2-1743531-3(GRAY)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED 0-XX-10 ± 0.2 10-XX-30 ± 0.25 30-XX ± 0.3 ANGLES ± 3°
		
3rd ANGLE PROJECTION		
MATERIAL		
SEE TABLE		FINISH

DWN : YD. LEE		CHK : BM JANG		APVD : CS LEE		PRODUCT SPEC		APPLICATION SPEC		WEIGHT	
Tyco Electronics		AMP KOREA.		kyungsan, korea		NAME		040/090 HYBRID 39P PLUG ASS'Y		FOR LIF CONNECTOR(LHD)	
SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO		A2		00779	
SCALE		2/1		SHEET		1 OF 1		REV		A	