







ISOMETRIC VIEW



<TABLE 2>

TYPE	WIRE SIZE (mm ²)	PART NO.	WIRE INSULATION DIAMETER (mm)	COLOR
MTII	0.35~0.5	964971-1	1.2~1.6	RED
	0.5~0.75	963530-1	1.4~1.9	GRAY
	1.0	964972-1	1.9~2.1	YELLOW
		963531-1	CAVITY PLUG	WHITE
JPT	0.35~1.0	828904-2	1.2~2.1	BLUE
	1.5~2.5	828905-1	2.2~3.0	WHITE
		828922-1	CAVITY PLUG	NATURAL
MCP	2.5~4.0	828985-1	3.0~3.7	GREEN
		828986-1	CAVITY PLUG	BROWN

NOTE

1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. DELIVERY CONDITION
3. APPLIED PLUG P/N: X-1743632-X
APPLIED PLUG P/N: 2483601-X FOR ONLY 1-1743636-2
APPLIED WIRE COVER P/N: X-1743638-X
4. APPLICABLE TAB CONTACT P/N: TABLE 1

C2	TERMINAL TYPE	CAVITY/CIRCUIT NO.
	JPT	1, 15, 29
	MCP	8, 22, 36
	MTII	REMAINING

5. APPLICABLE WIRE SEAL P/N:TABLE 2

CAP HSG	I-1743636-2	PBT-GF15	BLACK	EXPORT
CAP HSG	1743636-2	PBT-GF15	BLACK	-
DESCRIPTION	P/N	MATERIAL	COLOR	REMARK


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SJ CH01 CHK JW JUNG APVD HG CHO PRODUCT SPEC C108-61618 APPLICATION SPEC		 TE Connectivity	
DIMENSIONS: mm  3rd ANGLE PROJECTION		NAME CAP HSG FOR MT11 JPT MCP SEALED 36P CONN'R			
TOLERANCES UNLESS OTHERWISE SPECIFIED. 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		SIZE A2		CAGE CODE 00779	
MATERIAL SEE TABLE		WEIGHT		DRAWING NO C-1743636	
FINISH		CUSTOMER DRAWING		RESTRICTED TO - SCALE 2:1 SHEET 1 OF 2 REV C4	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET I	-	-	-

D



B

1471-9 (3/13)