

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC
DSDIST
—

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		RELEASED	12 DEC '06	YD.	JK
B		REVISED (ECR-08-001980)	24 JAN '08	KT	JK




LHD 3D VIEW




RHD 3D VIEW



RHD TYPE(0-1743710-2)



LHD TYPE(1-1743710-2)



NOTES:

1. GENERAL TOLERANCE IS ± 0.3
2. CONDITION OF DELIVERY

TYPE	LHD	RHD
ASS'Y P/NO.	1-1743710-2	1743710-2

NO.	COLOR	MATERIAL	DESCRIPTION	Q'TY
2	BLACK	PBT-GF20	LEVER	1
1	DARK GRAY	PBT-GF20	COVER LHD	1
1	BLACK	PBT-GF20	COVER RHD	1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING DEPARTMENT
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0-XX-10 ± 0.2 10-XX-30 ± 0.25 30-XX ± 0.3 ANGLES $\pm 3^\circ$
MATERIAL SEE TABLE	FINISH

DWN KT JUNG	CHK JW JUNG	APVD JK SONG	PRODUCT SPEC	APPLICATION SPEC	WEIGHT	CUSTOMER DRAWING
----------------	----------------	-----------------	--------------	------------------	--------	------------------

Tyco Electronics		AMP KOREA. kyungsan, korea	
NAME MQS/MCP6.3K HYBRID 26P COVER ASS'Y			
SIZE A2	CAGE CODE 00779	DRAWING NO 1743710	RESTRICTED TO -
SCALE 1/1		SHEET 1 OF 1	REV B