



REVISIONS				
P	LR	DESCRIPTION	DATE	OWN
B10		REVISED PER ECR-24-230423	25DEC2024	N.H. L.C



- 1 MATERIAL:
HOUSING: NYLON, UL94-V0
PIN: BRASS.
- 2 FINISH:
PIN: 80u" MIN. TIN PLATED ON CONTACT AREA.
- 3 COMPLY WITH GLOW WIRE REQUIREMENTS FOR PARTS OF
NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING
CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)
- 4 SKETCHES SHOW NO PINS MISSING.

5 "O" WITH PIN
"X" WITHOUT PIN.

O	X	O	O	O	X	O						7	NATURAL	27.72	1-1744525-7
O	O	O	O	O	X	O	X	O				9	NATURAL	35.64	3-1744525-9
O	O	X	O	O	X	O	X	O				9	NATURAL	35.64	2-1744525-9
O	O	O	X	O	X	O						7	NATURAL	27.72	1744525-7
X	O	X	O	X	O	X	O	X				9	NATURAL	35.64	1-1744525-9
X	O											2	NATURAL	7.92	1744525-2
O	O	O	O	O	O	O	O	O	X	O		11	NATURAL	43.56	1-1744525-1
O	X	O	X	O	X	O	X	O				9	NATURAL	35.64	1744525-9
O	X	O	O	O	O							6	NATURAL	23.76	2-1744525-6
O	X	O	X	O								5	NATURAL	19.80	2-1744525-5
O	X	O	O									4	NATURAL	15.84	2-1744525-4
O	X	O	O	O	X	O	O	O	O	O	O	12	NATURAL	47.52	1-1744525-2
O	O	X	O	O								5	NATURAL	19.80	1744525-5
O	O	X	O									4	NATURAL	15.84	1744525-4
O	X	O										3	NATURAL	11.88	1744525-3
1	2	3	4	5	6	7	8	9	10	11	12	NO. OF POSITIONS	COLOR	DIM A ±0.30	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT.									
			OWN JR. RUTH		22MAR13				
			CHK TOM MICHELUCCI		22MAR13				
DIMENSIONS:			TOLERANCES, UNLESS OTHERWISE SPECIFIED:						
mm			0 PLG ± 0.3						
			1 PLG ± 0.25						
			2 PLG ± 0.13						
			3 PLG ± 0.05						
			4 PLG ± - ± .30°						
MATERIAL			FINISH						
-			-						
CUSTOMER DRAWING			NAME						
			ECONOMY POWER CONNECTOR, RIGHT ANGLE HEADER, 3.96MM PITCH						
			SIZE						
			A2 00779						
			CAGE CODE						
			DRAWING NO						
			SCALE						
			N/A						
			SHEET						
			1 of 1						
			REV						
			B10						

1744525