

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT 2015 By Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.

REVISONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B3	REVISED	変更 ECR-23-185274	06SEP2023	AG	RK

△ TO BE MEASURED BETWEEN [T] AND 2
 △ TO BE MATE WITH PLUG HSG SMOOTHLY
 3 TO BE USE TAPPING SCREW JIS-B1115, OR 1122 (TYPE 2 OR 4) BEFORE SOLDER
 4 MATES WITH PLUG HSG P/N 173853, 173851
 △ CIRCUIT NUMBER

△ [T] 面より 2mm の範囲で測定
 △ 相手プラグハウジングと支障なく嵌合できる事
 3. プリント基板取付けは、JIS-B1115又は1122、M3X5のナベ(2又は4種)のタッピングネジで締め付け後半田付けする
 4. 嵌合する相手ハウジング型番: 173853, 173851
 △ 回路番号: 左図参照のこと

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差
 0 < x ≤ 10 : ±0.2
 10 < x ≤ 30 : ±0.25
 30 < x ≤ 100 : ±0.3
 ANGLE : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.
 DIMENSIONS: 単位: 寸 mm
 TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
 MATERIAL 材料 HOUSING: PBT CONTACT: BRASS
 FINISH 仕上
 SEE TABLE 表参照

DWN K.FURUYAMA 21APR2015	CHK Y.MITO 21APR2015	APVD R.KOMIYAMA 21APR2015	NAME 名称
PRODUCT SPEC 製品規格			070 SERIES MULTI LOCK I/O CONN. 30POSITION CAP ASSY STAND OFF H TYPE
APPLICATION SPEC 取付適用規格		WEIGHT 19.8 g	SIZE A2
CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO C=174458
SCALE 2:1		SHEET 1 of 1	REV B3

OBSOLETE	SELECTIVE-TIN [MATTE] PRE-TIN x 24	SELECTIVE GOLD x 6	6,8,19~22 (6極)	1~5,7,9~18,23~30 (24極)	NATURAL 自然色	2-5174458-1
OBSOLETE	SELECTIVE-TIN [MATTE] PRE-TIN x 21	SELECTIVE GOLD x 9	11~13,25~30 (9極)	1~10,14~24 (24極)	GRAY 灰色	1-5174458-6
OBSOLETE	TIN-LEAD PRE-TIN x 24	SELECTIVE GOLD x 6	6,8,19~22 (6極)	1~5,7,9~18,23~30 (24極)	NATURAL 自然色	2-174458-1
OBSOLETE	TIN-LEAD PRE-TIN x 21	SELECTIVE GOLD x 9	11~13,25~30 (9極)	1~10,14~24 (24極)	GRAY 灰色	1-174458-6
	PRE-TIN x 30		-	1~30 (全極)	GRAY 灰色	174458-6
	PRE-TIN x 30		-	1~30 (全極)	GREEN 緑色	174458-4
	PRE-TIN x 30		-	1~30 (全極)	NATURAL 自然色	174458-1
	SOLDERING SIDE 半田付け面	CONTACT SIDE 接触部側	△ GOLD PLATED CIRCUIT NO. 全めっき回路番号		△ PRE-TIN CIRCUIT NO. 全めっき回路番号	COLOR 色
	CONTACT FINISH コンタクト仕上					PART NUMBER 製品型番

1471-9 (1/15)

174458

B

A