



LOC	HT	DIST	OO	P	LTR	0	REVISIONS	DATE	28APR05	DMN	HXF	APVD	DF
							DESCRIPTION						



- NOTES:
1. MURATA COMPATIBLE, 2.0MM MATING HEIGHT.
  2. 100% ELECTRICAL TESTING FOR: CONTINUITY AND SHORTS, HI-POT AT 150 VDC FOR 100ms  
FREQUENCY RANGE: DC TO 6 GHz  
VSWR 1.4:1 MAX
  3. PRODUCT RATINGS:  
TEMPERATURE: -40 TO +90 DEG.C  
VOLTAGE: 60 VAC  
CHARACTERISTIC IMPEDANCE: 50 OHMS  
MATING DURABILITY: 30 CYCLES



AR	MM	DESCRIPTION	QTY	UNIT	ITEM
2	PC	UMCC TYPE I PLUG			1
		MINIATURE COAXIAL CABLE, 0.80 mm OD			2

THIS DRAWING IS A CONTROLLED DOCUMENT.

DMN: Hao Xiangfeng 28APR05  
 CHK: Fouli Zhou 28APR05

**tyco** Tyco Electronics Corporation  
**Electronics** KunShan, CHINA 215321

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLG	±
1 PLG	±
2 PLG	±
3 PLG	±
4 PLG	±
ANGLES	±
FINISH	±

DIMENSIONS: MM	APVD	DMN	HT	OO	P	LTR	0	DATE	28APR05	DMN	HXF	APVD	DF
OTHERWISE SPECIFIED:		DENVER WILLSON		PRODUCT SPEC		APPLICATION SPEC		WEIGHT		SCALE		SHEET	
SIZE		CASE CODE		DRAWING NO		RESTRICTED TO		SCALE		SHEET		REV	
A4		00779		1750109-2		-		1:1		1 OF 1		0	