






D

C





- △ □ 面から2mmの範囲で測定
- 嵌合相手ハウジング型 174514, 174516, 917981, 917992
 - 推奨取付ねじ: JIS B1115, B1122 タッピングねじ, なべ2種
呼び径3, 長さ6mm以下 (締付けトルク: 0.4N-m (4kg-cm) 以下)
 - 適用製品規格番号: 108-5280, 5342

△ 回路番号:
パワー回路 ①~⑩
シグナル回路 ⑪~④②



△ コンタクト仕上識別マーク

- △ MUST BE KEPT BETWEEN □ Z AND 2
- THE MATING PLUG HSG. PART NUMBER; 174514, 174516, 917981, 917992
 - RECOMMENDED MOUNTING SCREW; 3mm DIA, 6mm LENGTH (MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE; 0.4N-m (4kg-cm) MAX.)
 - APPLICABLE PRODUCT SPEC NO.; 108-5280, 108-5342
- △ CIRCUIT NUMBER
POWER CIRCUIT NO. ①~⑩
SIGNAL CIRCUIT NO. ⑪~④②
- △ MARKING FOR DISCERNMENT OF THE CONTACT FINISH



OBSOLETE	54	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 11	⑩	②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	4-5175446-6
OBSOLETE	59	PRE-TINNED × 31 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 2	— / —	⑩②③	GRAY 灰色	9-5175446-6
	58	PRE-TINNED × 40 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 16	— / —	⑩②③	GRAY 灰色	8-5175446-6
	58	PRE-TINNED × 26 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 16	— / —	⑩②③	NATURAL 自然色	8-5175446-1
OBSOLETE	54	PRE-TINNED × 26 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 17	⑤	②③④⑤	NATURAL 自然色	6-5175446-1
	54	PRE-TINNED × 25 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8	— / —	⑩②③	NATURAL 自然色	4-5175446-1
OBSOLETE	53	PRE-TINNED × 34 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 6	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	3-5175446-6
OBSOLETE	53	PRE-TINNED × 36 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 8	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	3-5175446-1
	52	PRE-TINNED × 34 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 32	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	2-5175446-6
	52	PRE-TINNED × 10 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 32	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	2-5175446-1
OBSOLETE	55	PRE-TINNED × 10 SELECTIVE-TIN (MATTE)	SELECTIVE GOLD × 12	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	5-5175446-1
	9	TIN-LEAD PRE-TINNED × 40	SELECTIVE GOLD × 2	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	9-175446-6
OBSOLETE	8	TIN-LEAD PRE-TINNED × 26	SELECTIVE GOLD × 16	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	8-175446-6
OBSOLETE	8	TIN-LEAD PRE-TINNED × 26	SELECTIVE GOLD × 16	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	8-175446-2
OBSOLETE	8	TIN-LEAD PRE-TINNED × 26	SELECTIVE GOLD × 16	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	8-175446-1
OBSOLETE	7	TIN-LEAD PRE-TINNED × 39	SELECTIVE GOLD × 3	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	7-175446-5
	6	TIN-LEAD PRE-TINNED × 39	SELECTIVE GOLD × 17	⑨	②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	6-175446-1
	5	TIN-LEAD PRE-TINNED × 25	SELECTIVE GOLD × 12	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	5-175446-1
	4	TIN-LEAD PRE-TINNED × 30	SELECTIVE GOLD × 11	⑩	②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	4-175446-6
OBSOLETE	4	TIN-LEAD PRE-TINNED × 31	SELECTIVE GOLD × 8	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	4-175446-1
OBSOLETE	3	TIN-LEAD PRE-TINNED × 34	SELECTIVE GOLD × 6	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	3-175446-6
	3	TIN-LEAD PRE-TINNED × 36	SELECTIVE GOLD × 8	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	3-175446-1
	2	TIN-LEAD PRE-TINNED × 34	SELECTIVE GOLD × 32	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	2-175446-6
	0	PRE-TINNED 銀めっき × 42	—	— / —	⑩②③④⑤⑥⑦⑧⑨④②	GRAY 灰色	175446-6
	1	SELECTIVE-TIN (MATTE) 銀めっき × 42	SELECTIVE-TIN (銀めっき) × 42	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	175446-2
	0	PRE-TINNED 銀めっき × 42	—	— / —	⑩②③④⑤⑥⑦⑧⑨④②	NATURAL 自然色	175446-1
△ MARKING マ-キング	SOLDERING SIDE 半田付け面		CORCTACT SIDE 接触部	POWER CIRCUIT NO. パワー回路	SIGNAL CIRCUIT NO. シグナル回路	HOUSING COLOR ハウジング色	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 寸
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED
公差
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

0.4
0.5
X
R

MATERIAL
材料
HOUSING: PBT
CONTACT: BRASS

FINISH
仕上
SEE TABLE
表参照

DWN
M. KADOSAKI
17MAY05

CHK
T. SHINOHARA
17MAY05

APVD
K. BETSUJI
17MAY05

NAME
氏名

PRODUCT SPEC
製品規格
SEE NOTE 4

APPLICATION SPEC
取付適用規格

SIZE
寸法

CAGE CODE
庫番

DRAWING NO
図番

RESTRICTED TO
制限

WEIGHT
重量

21.3 g

CUSTOMER DRAWING

SCALE
尺度

2:1

SHEET
シート

1 OF 1

REV
改訂

N11

4805 (1/15)