





WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECN-23-241206	27NOV2023	LP	PD



RECOMMENDED PCB LAYOUT
SCALE 16:1

HOUSING CAP CENTER CONTACT	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204
DIELECTRIC	PTFE FLOUROCARBON PER ASTM-D-1457	N/A
COMPONENT	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. PROSPER 20NOV2023	 TE Connectivity				
DIMENSIONS: in		CHK P. D'AMATO 20NOV2023					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.005 4 PLC ± ANGLES ±1° FINISH	APVD P. D'AMATO 27NOV2023	NAME SMC RT ANGLE PRINTED CIRCUIT BOARD JACK RECEPTACLE STRAIGHT TERMINAL -				
		PRODUCT SPEC -					
MATERIAL SEE TABLE -	FINISH SEE TABLE -	APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C-1757211	RESTRICTED TO -	
		WEIGHT -	CUSTOMER DRAWING		SCALE 8:1	SHEET 1 OF 1	REV B