






|     |      |           |     |             |      |     |     |
|-----|------|-----------|-----|-------------|------|-----|-----|
| LOC | DIST | REVISIONS |     |             |      |     |     |
| DW  | —    | P         | LTR | DESCRIPTION | DATE | DWN | APV |
|     |      |           | —   | SEE SHEET 1 | —    | —   | —   |




DETAIL B  
 (SCALE; 2:1)  
 (HEADER CONNECTOR MOUNTING LAYOUT DETAIL)



DETAIL D

---

(SCALE; 4:1)



DWN

CHK




APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

|                                                                                       |        |                                                                                       |  |
|---------------------------------------------------------------------------------------|--------|---------------------------------------------------------------------------------------|--|
| DIMENSIONS:                                                                           |        | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED                                              |  |
| mm                                                                                    |        |                                                                                       |  |
|  | 0 PLC  | ± 0.5                                                                                 |  |
|                                                                                       | 1 PLC  | ± 0.5                                                                                 |  |
|                                                                                       | 2 PLC  | ± 0.5                                                                                 |  |
|                                                                                       | 3 PLC  | ± 0.5                                                                                 |  |
|                                                                                       | 4 PLC  | ± 0.5                                                                                 |  |
|                                                                                       | ANGLES | ± 1°                                                                                  |  |
| MATERIAL                                                                              |        | FINISH                                                                                |  |
|  |        |  |  |




TE Connectivity

|      |                                                                                |
|------|--------------------------------------------------------------------------------|
| NAME | SHIELD FRAME ASSY, TOP MOUNT H=0.25<br>CARD PUSH TYPE<br>ExpressCARD CONNECTOR |
|------|--------------------------------------------------------------------------------|

|      |           |            |            |
|------|-----------|------------|------------|
| SIZE | CAGE CODE | DRAWING NO | RESTRICTED |
| A3   | 00779     | C-1759152  | —          |


|                  |       |       |       |        |     |    |
|------------------|-------|-------|-------|--------|-----|----|
| CUSTOMER DRAWING | SCALE | 1 : 1 | SHEET | 2 OF 7 | REV | D1 |
|------------------|-------|-------|-------|--------|-----|----|

1759152-1 : AS SHOWN



- △ RECOMENDED TIGHTENING TORQUE 0.10Nm MAX
- △ SCREW LENGTH(FROM MOUNT SURFACE)
- △ NO COMPONENT AND NO SIGNAL LINE AREA
- △ GROUNDING PAD
- △ SOLDERING PAD
- △ CONNECTOR AREA (STAND OFF 0.25)
- △ STAND OFF 0
- △ NO COMPONENT AREA

REFERENCE FIGURE WHICH ATTACHED  
HEADER ASSEMBLY



THIS DRAWING IS A CONTROLLED DOCUMENT.

|                   |                                                                                                                                  |
|-------------------|----------------------------------------------------------------------------------------------------------------------------------|
| DIMENSIONS:<br>mm | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± 0.5<br>1 PLC ± 0.5<br>2 PLC ± 0.5<br>3 PLC ± 0.5<br>4 PLC ± 0.5<br>ANGLES ± 1° |
| MATERIAL          | FINISH                                                                                                                           |

|                  |                  |        |
|------------------|------------------|--------|
| DWN              | CHK              | APVD   |
| PRODUCT SPEC     | APPLICATION SPEC | WEIGHT |
| CUSTOMER DRAWING |                  |        |

TE Connectivity

NAME  
SHIELD FRAME ASSY, TOP MOUNT H=0.25  
CARD PUSH TYPE  
ExpressCARD CONNECTOR

|              |                    |                       |                 |
|--------------|--------------------|-----------------------|-----------------|
| SIZE<br>A3   | CAGE CODE<br>00779 | DRAWING NO<br>1759152 | RESTRICTED TO   |
| SCALE<br>1:1 |                    |                       | SHEET<br>3 OF 7 |
| REV<br>D1    |                    |                       |                 |

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .



COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

DW

P

LTR

DESCRIPTION

DATE

DWN

APVD

-





SEE SHEET 1

-

-

-

1759152-2 : AS SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

SHIELD FRAME ASSY, TOP MOUNT H=0.25  
CARD PUSH TYPE  
ExpressCARD CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

1759152

SCALE

1:1

SHEET

4

OF






7

REV

D1



| LOC | DIST | REVISIONS |     |             |      |      |
|-----|------|-----------|-----|-------------|------|------|
| DW  |      | P         | LTR | DESCRIPTION | DATE | APVD |
|     |      | -         | -   | SEE SHEET 1 | -    | -    |

1759152-2 : AS SHOWN




|                                                                                                  |  |                  |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
|--------------------------------------------------------------------------------------------------|--|------------------|--|------------------------------------------------------------------------------------------------------------------|--|--------------------|--|-------------------------|--|--------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                           |  | DWN              |  | <div> TE Connectivity</div> |  |                    |  |                         |  |                    |  |
| DIMENSIONS:<br>mm                                                                                |  | CHK              |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
| <div></div> |  | APVD             |  | NAME<br><br>SHIELD FRAME ASSY, TOP MOUNT H=0.25<br>CARD PUSH TYPE<br>ExpressCARD CONNECTOR                       |  |                    |  |                         |  |                    |  |
|                                                                                                  |  | PRODUCT SPEC     |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
|                                                                                                  |  | APPLICATION SPEC |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
|                                                                                                  |  | WEIGHT           |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
|                                                                                                  |  | CUSTOMER DRAWING |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                           |  | 0 PLC ± 0.5      |  | SIZE<br>A3                                                                                                       |  | CAGE CODE<br>00779 |  | DRAWING NO<br>C-1759152 |  | RESTRICTED TO<br>— |  |
| 1 PLC ± 0.5                                                                                      |  |                  |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
| 2 PLC ± 0.5                                                                                      |  |                  |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
| 3 PLC ± 0.5                                                                                      |  |                  |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
| 4 PLC ± 0.5                                                                                      |  |                  |  |                                                                                                                  |  |                    |  |                         |  |                    |  |
| ANGLES ± 1°                                                                                      |  | FINISH           |  | SCALE<br>1:1                                                                                                     |  | SHEET<br>5 OF 7    |  | REV<br>D1               |  |                    |  |

1759152-2: AS SHOWN



- 9 RECOMENDED TIGHTENING TORQUE 0.10Nm MAX
- 10 SCREW LENGTH(FROM MOUNT SURFACE)
- 11 NO COMPONENT AND NO SIGNAL LINE AREA
- 12 GROUNDING PAD
- 13 SOLDERING PAD
- 14 CONNECTOR AREA (STAND OFF 0.25)
- 15 STAND OFF 0
- 16 NO COMPONENT AREA

REFERENCE FIGURE WHICH ATTACHED  
HEADER ASSEMBLY



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

|        |       |
|--------|-------|
| 0 PLC  | ± 0.5 |
| 1 PLC  | ± 0.5 |
| 2 PLC  | ± 0.5 |
| 3 PLC  | ± 0.5 |
| 4 PLC  | ± 0.5 |
| ANGLES | ± 1°  |
| FINISH |       |

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

NAME  
SHIELD FRAME ASSY, TOP MOUNT H=0.25  
CARD PUSH TYPE  
ExpressCARD CONNECTOR

SIZE  
A3

CAGE CODE  
00779

DRAWING NO  
 1759152

RESTRICTED TO

SCALE  
1:1

SHEET  
6 OF 7

REV  
D1



THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

ALL RIGHTS RESERVED.



COPYRIGHT - By -

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

- SEE SHEET 1

ExpressCard  
EJECTOR

TRAY

AIR CAP

CARTON

TAPE

PACKAGE  
BELT

17. MATERIAL:

TRAY: PS, COLOR: CLEAR, t=0.8

18. CARTON DIMENSION: 363X320X152

16

10

160

1759152-2

16

10

160

1759152-1

PCS/TRAY

TRAY/CARTON

TOTAL Q'TY

PARTS NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC


APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:0 PLC ± 0.5  
1 PLC ± 0.5  
2 PLC ± 0.5  
3 PLC ± 0.5  
4 PLC ± 0.5  
ANGLES ± 1°

MATERIAL

FINISH



TE Connectivity

NAME

SHIELD FRAME ASSY, TOP MOUNT H=0.25  
CARD PUSH TYPE  
ExpressCARD CONNECTOR

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1759152

SCALE

NON

SHEET

7 OF 7

REV

D1