







REVISIONS					
REV	DATE	DESCRIPTION	BY	CHK	APPV
G4	07APR15	REVISION ECR-15-004544	KF	RK	
G5	06DEC2022	REVISION PER ECR-22-154840	RK	MT	



- 注記
- △ X から2mmの範囲で測定
 - 嵌合相手ハウジング型 175109, 175110, 175111
 - 推奨取付ねじ: JIS B1115, B1122 タップピンねじ, なべ2種
呼び径3, 長さ6mm以下 (締付けトルク: 0.4N-m(4kg-cm)以下)
 - 適用製品規格番号: 108-5280
 - △ コンタクト仕上識別マーク

- NOTES
- △ MUST BE KEPT BETWEEN X AND 2
 - THE MATING PLUG HSG. PART NUMBER; 175109, 175110, 175111
 - RECOMMENDED MOUNTING SCREW; 3mm DIA, 6mm LENGTH (MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE; 0.4N-m(4kg-cm) MAX.)
 - APPLICABLE PRODUCT SPEC NO. 108-5280
 - MARKING FOR DISCERNMENT OF THE CONTACT FINISH



MARKING	CONTACT FINISH	POWER CIRCUIT NO	SIGNAL CIRCUIT NO	COLOR	PART NUMBER
△	PRE-TIN × 56 SELECTIVE-TIN (MATTE) SELECTIVE GOLD × 8	57~64		GRAY 灰色	2-5176122-6
	SEE CUSTOMER DRAWING 9-176122-6				
	PRE-TIN × 56 TIN-LEAD SELECTIVE GOLD × 8	57~64		GRAY 灰色	2-176122-6
	PRE-TIN			ORANGE オレンジ色	176122-8
	PRE-TIN			GRAY 灰色	176122-6
	SELECTIVE-TIN (MATTE) SELECTIVE-TIN (BRIGHT)			GRAY 灰色	176122-1
△	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	POWER CIRCUIT NO パワー回路	SIGNAL CIRCUIT NO シグナル回路	GOLD PLATED CIRCUIT NO 金めっき回路番号

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIN M. KADOSAKI 120CT05	APVD T. SHINOHARA 120CT05	NAME 氏名	TE Connectivity
CHK K. BETSUJI 120CT05	NAME 氏名	64POS. CAP HOUSING ASSY .040/.070 SERIES HYBRID I/O CONN.	RESTRICTED TO
PRODUCT SPEC	APPLICATION SPEC	SIZE A1	SCALE 2:1
APPLICATION SPEC	WEIGHT	CAGE CODE 00779	SHEET 1 of 1
FINISH 仕上	SEE TABLE	DRAWING NO. 176122	REV G5

GENERAL TOLERANCE: 0<<10 : ±0.2, 10<<30 : ±0.25, 30<<100 : ±0.3, ANGLES : ±3°

MATERIAL: HOUSING : PBT, CONTACT : BRASS

CUSTOMER DRAWING