



26P, 20P

28P, 22P, 16P

注 記

1. 適用コネクタ型番 : X-173977-X (リセ)

NOTE

1. CONNECTOR P/N : X-173977-X (RECC)

34.3	28.0	14	30	3-176236-0
32.3	26.0	13	28	2- -8
30.3	24.0	12	26	2- -6
28.3	22.0	11	24	2- -4
26.3	20.0	10	22	2- -2
24.3	18.0	9	20	2- -0
22.3	16.0	8	18	1- -8
20.3	14.0	7	16	1-176236-6
A	B	N	POS 極数	型番 P/N

LTR	変更 (REVISION RECORD)	DR	CHK	DATE
A	変更 J-12425	Y.K	H.K	13/SEP/90
0	作成 J-12667	H.K	R.N	13/SEP/90

Copyright ©1990 AMP (Japan), LTD. ALL RIGHTS RESERVED.	Copyright ©1990 AMP (Japan), LTD. ALL RIGHTS RESERVED.
材料 (MATERIAL) 66ナイロン樹脂	色 (COLOR) 青色
DR. Y. KODAIRA	DE. H. KANAI
CHK. H. KANAI	APP. R. NISHIMURA

一般公差 (GENERAL TOLERANCES) 10mm以下: ±0.2 10mm以上: ±0.25 角度: ±0.3 表面粗さ: Ra 1.25		名称 (NAME) HOLDER CT DOUBLE ROW CONN. ホルダー CTダブルローコネクタ	
SIZE	LOC	番号 (NO.)	
A3	J	C-176236	
尺取 (SCALED)	REV.	SHEET	
NTS	A	1 OF 1	

AMP

Tokyo, Japan