



NUMBER C-176394
METRIC
3rd ANGLE PROJECTION
PRINT DIST
DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT



- 注:
- 1. 材料 : HSG - 66ナイロン樹脂UL94V-0
ポスト - 金メッキ付黄銅
 - 2. 適用製品規格 : 108-5218
 - 3. 嵌合相手製品型番 : P/N 176392

- NOTES:
- 1. MATERIAL: HOUSING - 66 NYLON (UL94V-0)
POST - GOLD-PLT BRASS
 - 2. PRODUCT SPEC.; 108-5218
 - 3. APPLICABLE RECEPTACLE; P/N 176392



RECOMMENDABLE P.C. BOARD LAYOUT
推奨基板寸法
(板厚 0.8-1.6)
(PCB THK: 0.8-1.6)

F	変更	FJ00-1400-97	2.0	9/16/97
E	キンク変更	FJ00-1343-97	E.C.J.T	9/8/97
D	キンク変更	J-1780	T.F.S.K	12/15/92
C	キンク変更	J-1486	S.K.J.T	9/4/92
B	変更	J-1013	T.F.S.K	11/28/92
A	変更	J-12466	T.F.S.K	6/26/90
O	作成	J-12272	T.F.S.K	2/1/90
LTR	REVISION RECORD	DR	CHK	DATE

Copyright ©19 年		Copyright ©19 年	
AMP (Japan), LTD.		AMP (Japan), LTD.	
ALL RIGHTS RESERVED.		ALL RIGHTS RESERVED.	
WIRE RANGE	INSULATION DIA	NAME ボックス仕様ポストヘッダーアッセンブリ (水平型)	
mm ² CAVG -)	mmφ	金メッキ タイプ (AMP CT コネクタ 2mmピッチ)	
MATERIAL	FINISH	POST HEASER ASS'Y (BOX-H)	
SEE NOTE 1	SEE NOTE 1	GOLD PLT TYPE (AMP CT CONNECTOR 2mm PITCH)	
注1参照	注1参照	GENERAL TOLERANCE	
DR. T.FURUYA 1/31/'90	DE. T.FURUYA	SIZE LOC NUMBER	
CHK. S.KIKUCHI 2/1/'90	APP. S.Kikuchi 9/16/97	0<≦10 : ±0.2	
		10<≦30 : ±0.25	
		30<≦100 : ±0.3	
		ANGLES : ±3°	

AMP		AMP (JAPAN), LTD.	
		Tokyo, Japan	
C-176394		C-176394	
SCALE 5 - 1		REV. F	
SHEET 1 OF 1		SHEET 1 OF 1	

CUSTOMER DRAWING