



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
H1		REVISE AS PER ECR-19-018622	29NOV2019	AL	HL



6 Pos. (P/N: 3-176890-6)



12 Pos. (P/N: 7-176890-2)


注記

1. 包装規格 : 107-5123-5

NOTE

1. PACKAGING SEPC:107-5123-5

330	80	29	26	300	12	7.45	6.25	24	750	16	7-174821-6	7-176890-6
330	100	22.4	16.4	300	12	7.45	6.25	24	750	12	7-174821-2	7-176890-2
330	80	29	26	300	12	5.45	4.25	24	1000	24	5-174821-4	5-176890-4
330	80	29	26	300	12	5.45	4.25	24	1000	22	5-174821-2	5-176890-2
330	80	29	26	300	12	5.45	4.25	24	1000	20	5-174821-0	5-176890-0
330	80	29	26	300	12	5.45	4.25	24	1000	18	4-174821-8	4-176890-8
330	80	29	26	300	12	5.45	4.25	24	1000	16	4-174821-6	4-176890-6
330	100	22.4	16.4	300	12	5.45	4.25	16	1000	14	4-174821-4	4-176890-4
330	80	21	18	300	12	5.45	4.25	16	1000	12	4-174821-2	4-176890-2
330	80	21	18	300	12	5.45	4.25	16	1000	10	4-174821-0	4-176890-0
330	80	21	18	300	12	5.45	4.25	16	1000	6	3-174821-6	3-176890-6
330	80	29	26	300	12	6.95	5.75	24	750	16	1-174821-6	1-176890-6
D 2	D 1	W 2	W 1	M	P	B	A	C	QTY/ REEL	Pos	CONNECTOR P/N	TAPING P/N



WITHOUT POLYAMIDE TAPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	S.KANEKI	22JUN90		TE Connectivity
CHK	J.TANIGAWA	22JUN90		
APVD	S.KUBOUCHI	22JUN90	NAME	1.25 FP CONNECTOR (B-TO-B) ON TAPING (EMBOSS) DOUBLE ROW POST HDR ASS'Y SMT TYPE
PRODUCT SPEC	108-5246		APPLICATION SPEC	
WEIGHT			SIZE	A3
CUSTOMER DRAWING			CAGE CODE	00779
			DRAWING NO	C=176890
			RESTRICTED TO	
			SCALE	
			SHEET	1 of 2
			REV	H1

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT By -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

EXCEPT 6 Pos. AND 12 Pos.

WITH POLYAMIDE TAPE

330	100	30.4	24.4	300	12	6.95	5.75	24	700	14	1-174821-4	176890-4
330	80	29	26	300	12	7.45	6.25	24	750	16	7-174821-6	9-176890-6
330	100	22.4	16.4	300	12	7.45	6.25	24	700	12	7-174821-2	9-176890-2
330	80	29	26	300	12	5.45	4.25	24	1000	24	5-174821-4	8-176890-4
330	80	29	26	300	12	5.45	4.25	24	1000	22	5-174821-2	8-176890-2
330	80	29	26	300	12	5.45	4.25	24	1000	20	5-174821-0	8-176890-0
330	80	29	26	300	12	5.45	4.25	24	1000	18	4-174821-8	6-176890-8
330	80	29	26	300	12	5.45	4.25	24	1000	16	4-174821-6	6-176890-6
330	100	22.4	16.4	300	12	5.45	4.25	24	1000	14	4-174821-4	6-176890-4
330	80	21	18	300	12	5.45	4.25	16	1000	12	4-174821-2	6-176890-2
330	80	21	18	300	12	5.45	4.25	16	1000	10	4-174821-0	6-176890-0
330	80	21	18	300	12	5.45	4.25	16	1000	6	3-174821-6	2-176890-6
330	80	29	26	300	12	6.95	5.75	24	750	16	1-174821-6	176890-6
D2	D1	W2	W1	M	P	B	A	C	QTY/REEL	Pos	CONNECTOR P/N	TAPING P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 22JUN90

CHK S.KANEKI

J.TANIGAWA

APVD 22JUN90

S.KUBOUCHI

PRODUCT SPEC

APPLICATION SPEC

108-5246

WEIGHT

CUSTOMER DRAWING

 NAME  
 1.25 FP CONNECTOR (B-TO-B) ON TAPING (EMBOSS)  
 DOUBLE ROW POST HDR ASS'Y SMT TYPE

RESTRICTED TO

SIZE CAGE CODE DRAWING NO

A3 00779 C=176890

SCALE SHEET 2 of 2 REV H1

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

 0 PLC ±  
 1 PLC ±  
 2 PLC ±  
 3 PLC ±  
 4 PLC ±  
 ANGLES ±

MATERIAL FINISH

1470-19 (1/15)