




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-24-213594	01JUL2024	RK	FJS

D


C

B

A




VIEW A-A
RECOMMENDED PC BOARD LAYOUT



RECOMMENDED
PANEL CUTOUT

1. CONTACT CAVITIES IDENTIFIED BY CHARACTERS ON FRONT AND REAR FACES OF CONNECTOR.
2. #6 FASTNER RECOMMENDED FOR MOUNTING.
3. CONTACT BODY: .000030 MIN PRECIOUS METAL PLATE FOR A LENGTH OF .250 MIN FROM MATING END, WITH REMAINDER TO BE GOLD FLASH, BOTH OVER .000050 MIN NICKEL.
CONTACT POST: .000100 MIN TIN OVER MIN COPPER.
4. PC BOARD HOLE PATTERN IS DEFINED RELATIVE TO CONNECTOR C.L. AND PANEL MOUNTING FACE INDICATED.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 10/4/06		 TE Connectivity			
		CHK S HEADER 10/4/06					
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD S HEADER 10/4/06		NAME	
		0 PLC ± -		RECEPTACLE ASSEMBLY, POSTED, RT ANGLE, STD SEX, SIZE 17-16, SERIES 1, CPC			
		1 PLC ± -		-			
		2 PLC ± .03		-			
		3 PLC ± .010		-			
		4 PLC ± -		PRODUCT SPEC		-	
		ANGLES ± ±		APPLICATION SPEC		-	
MATERIAL		FINISH		WEIGHT		SIZE	RESTRICTED TO
-		-		-		A2 00779	-
				CUSTOMER DRAWING		DRAWING NO	
						C=1776904	
				SCALE		SHEET	REV
				2:1		1 of 1	C

1776904

B

A