



ロックタイプII LOCK TYPE II






表1 (TABLE 1)
トレードマーク
(TRADE MARK)

トレードマーク (TRADE MARK)	生産場所 (MANUFACTURING PLACE)
—AMP OR AMP	日本 (JAPAN)
—+AMP OR AMP	中国 (CHINA(PRC))
*AMP OR AMP	韓国 (KOREA)

断面 "A-A"
(SECT)

C6	REVISED ECR-23-169773	M.G	D.Z	20NOV 19
C5	REVISED PER ECR-19-017851	SM	D.Z	14NOV 2014
C4	REVISED ECR-14-017020	W.W	D.Z	14SEP 2014
C3	REVISED ECR-14-013449	W.W	D.Z	23DEC 2013
C2	REVISED ECR-13-019881	A.Z	D.Z	NOV16 2012
C1	REVISED ECR-12-019829	A.Z	F.M	NOV16 2012
C	変更 FJ00-1369-01	OK	AS	17DEC 2012
B	変更 FJ00-0242-00	OK	AS	17DEC 2012
LTR	変更 (REVISION RECORD)	DR	CHK	DATE

材料 (MATERIAL)	仕上 (FINISH)
5/8 タイム (UL 94V-0) 5/8 NYLON (UL 94V-0)	上
DR. 20 JUL '94 N. NAGASHIMA	DE. 20 JUL '94 M. SHINDO
CHK. 5 AUG '94 M. SHINDO	APP. 5 AUG '94 Y. KASHIWA

本図ロックタイプIを示す AS SHOWN LOCK TYPE I

NOTES,

- PRODUCT SPEC. 108-5410
- APPLICABLE CONTACT P/N
REC CONTACT: 177915-□ (*20-16AWG)
177914-□ (*26-22AWG)

回路番号
(CIRCUIT No.)

- MATING CONN. P/N
CAP H56: 179467-□ (FREE HANGING)
TAB CONTACT: 177917-□ (*20-16AWG)
177916-□ (*26-22AWG)

- APPLICABLE PLATE P/N: 177920-□
- INSTRUCTION SHEET: 411-5638

SEE TABLE 1

- ALL PARTS MEET RTI ELECTRICAL RATING OF 105C
ACCORDING TO UL 1777

- PART 5-177902-1 COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30 (GWT)


- PART 177902-7 COMPLY WITH HOT WIRE REQUIREMENT, PA66, UL 94V-0. HOT WIRE IGNITION (HW) VERSION ARE MOLDED IN A RESIN THAT COMPLIES WITH THE HOT WIRE IGNITION TEST 109-3026 AND ARE RECOMMENDED FOR USE WITH HW HOUSING THAT ALSO COMPLY.

- Preliminary-not for production

- APPLICATION SPEC: 114-5175

トレード・マーク
(TRADE MARK)

回路番号
(CIRCUIT No.)



注: 1. 適用製品規格: 108-5410

2. 適用コンタクト型番

リセ・コンタクト: 177915-□ (*20-16AWG)
177914-□ (*26-22AWG)

3. 嵌合相手側製品型番

キャップ・ハウジング: 179467-□ (自由吊りタイプ)
タブ・コンタクト: 177917-□ (*20-16AWG)
177916-□ (*26-22AWG)

4. 運用プレート型番: 177920-□

5. 取扱説明書: 411-5638

※ 表1参照

M.G

AMP

Tyco Electronics AMP K.K.
Kawasaki, Japan

名称 (NAME)	AMP POWER DOUBLE LOCK CONN.
8極 3.96mmピッチ プラグハウジング (2列タイプ)	
AMP POWER DOUBLE LOCK CONN. 3.96mm PITCH PLUG HOUSING 8 Pos (DBL ROW)	
一般公差	SIZE LOC 番号 (No.)
10mm ±0.2 10mm ±0.25 10mm ±0.3	B J C-177902
尺取 (SCALE)	REV. C6 SHEET 1 OF 1