





NUMBER 178140



METRIC


DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST



推奨基板取付け寸法  
PC 基板厚: 1.6±0.1  
(非累積公差)  
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN  
PC BOARD THICKNESS: 1.6±0.1  
(NOT ACCUMULATE TOLERANCE)  
(CONNECTOR MOUNT SIDE)



NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: BLACK  
CONTACT: COPPER ALLOY  
RETENTION LEG: COPPER ALLOY
- FINISH (CONTACT AREA): 0.38 μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 0.76 μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
- FINISH (RETENTION LEG): TIN-LEAD PLATED (CONTACT TAIL) OVER NICKEL
- FOR DRAWER
- FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL

注記

- 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂 (94V-0), 色: 黒  
コンタクト: 銅合金  
リテンションレグ: 銅合金
- めっき: コンタクト 全面 Ni 下地 接触部 0.38 μm MIN 金めっき
- めっき: コンタクト 全面 Ni 下地 接触部 0.76 μm MIN 金めっき
- めっき: コンタクト 全面 Ni 下地 接触部 2.0 μm MIN スズめっき
- めっき: リテンションレグとコンタクト半田付部 ニッケル下地の上に半田めっき
- ドロー用
- めっき: リテンションレグとコンタクト半田付部 ニッケル下地の上にスズめっき

A ROW		X	Y	△7 △4	3-178140-5
B ROW		X	Y	△7 △3	3-178140-3
A ROW		Y	Y	△7 △2	3-178140-2
A ROW		Y	Y	△7 △4	2-178140-5
B ROW		Y	Y	△7 △3	2-178140-3
B ROW		Y	Y	△7 △2	2-178140-2
A ROW		X	X	△7 △2	△6 4-178140-2
A ROW		X	X	△7 △4	1-178140-5
B ROW		X	X	△7 △3	1-178140-3
B ROW		X	X	△7 △2	1-178140-2
KEYING LOCATION		A ROW KEYING	B ROW KEYING	FINISH	製品番号 PART NO.

					<b>TE</b> TE Connectivity	
					DYNAMIC D-3200 5.08X7.62PITCH(V) 6 POS.HDR CONN.ASS'Y	
					NAME	
					DYNAMIC D-3200 5.08X7.62PITCH(V) 6 POS.HDR CONN.ASS'Y	
					WIRE RANGE	
					mm?(AWG - )	
					INSULATION DIA	
					mmφ	
					MATERIAL	
					SEE NOTE 注記参照	
					FINISH	
					SEE NOTE 注記参照	
					DR. 19 APR 94 DE. 19 APR 94	
					N. Matsubara N. Matsubara	
					CHK. 20 APR 94 APP. 20 APR 94	
					S. MANABE S. MANABE	
					F1 REVISED PER ECO-11-005030 RK HMR 23MAR 11	
					LTR REVISION RECORD DR CHK DATE	
					一般公差 (GENERAL TOLERANCE)	
					10以下: ±0.3	
					10以上 30以下: ±0.4	
					30以上 100以下: ±0.45	
					角度: ±3°	
					SIZE LOC NUMBER	
					A3 J C=178140	
					SCALE REV. SHEET	
					2-1 F1 1 OF 1	