


NUMBER 178327



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

コネクタ外形
OUTLINE OF HEADER HOUSING

スルーホール 2-φ2
DIA2±0.1 2PLACES

ラウンド 2-φ3MIN
ROUND DIA3MIN 2PLACES

16-φ1.1
DIA1.1±0.1 16PLACES

推奨基板取付け寸法

PC 基板厚: 1.6±0.1
(非累積公差)
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN

PC BOARD THICKNESS: 1.6±0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

NOTES

1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- △ FINISH (CONTACT AREA): 0.38μm PdNi & Au PLATING OVER NICKEL
- △ FINISH (CONTACT AREA): 0.76μm PdNi & Au PLATING OVER NICKEL
- △ FINISH (CONTACT AREA): 2.0 μm MIN TIN
PLATED OVER NICKEL
- △ FINISH (RETENTION LEG): TIN LEAD PLATED
(CONTACT TAIL) OVER NICKEL
- △ FINISH (RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL
7. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE THEY DON'T SHOW DETAILS
- △ THE DATE CODE SHOW PRODUCTION LOT BY NUMBER. THE NUMBER MAKE UP THE NUMBER OF FOUR COLUMNS OR FIVE COLUMNS. (INCLUDE THE ALPHABET)

△	△	178327-6
△	△	178327-5
△	△	178327-3
△	△	178327-2
(FINISH)		製品番号 (PART NO.)

F	REVISED PER ECR-25-250788	F.Z	R.B	16 JAN 2025
E3	REVISED	N.W.K.	Z.X.X	
LTR	REVISION RECORD	DR	CHK	DATE

WIRE RANGE		INSULATION DIA	NAME	
mm (AWG)		mm	16 POS DOUBLE ROW	
MATERIAL SEE NOTE 注記参照		FINISH SEE NOTE 注記参照	VERTICAL HDR ASS'Y FOR DYNAMIC D-3100	
DR. 19 APR 94 N. Matsubara		DE. 19 APR 94 N. Matsubara	一般公差 (GENERAL TOLERANCE)	SIZE LOC NUMBER
CHK. 20 APR 94 S. MANABE		APP. 20 APR 94 S. MANABE	10mm ±0.3 10mm 30mm ±0.4 30mm 100mm ±0.45 100mm ±3	A3 J C-178327
			SCALE	REV. SHEET
			2-1	F 1 OF 1

(CUSTOMER DRAWING) 顧客用図面