

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C1	ECR-25-234144	06FEB2025	KD	D, Z







 TABLE 2	
TRADE MARK	MANUFACTURING PLACE
-AMP OR $\bar{\text{AMP}}$	JAPAN
-+AMP OR $\bar{\text{AMP}}^+$	CHINA
$\pm$ AMP OR $\bar{\text{AMP}}^{\pm}$	KOREA


NOTE.

1. GENERAL TOLERANCE: ± 0.3 , $\pm 3^\circ$
2. RECOMMENDED PCB LAYOUT: SEE FIG.1
3. APPLICABLE PCB THICKNESS: 1.6mm
4. MATING CONNECTOR P/N
- PLUG HSG: *-177905-*, 2005255-*

 TRADE MARK: SEE TABLE 2



SECTION B-B



SECTION C-C




FIG. 1

COPPER ALLOY TIN PLATED	NYLON GLASS FILLED (UL94V-0)	BLUE	179843-6
		YELLOW	179843-4
		NATURAL	179843-1
TAB CONTACT ①	HOUSING ②	COLOR	P/N
MATERIAL			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22 JAN 2025 CHEON KI DEOK CHK -		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: APVD 06 FEB 2025 ZHANG DANIEL PRODUCT SPEC 108-5410 APPLICATION SPEC -		NAME AMP POWER DBL LOCK CONN 3.96mm PITCH 12P TAB HEADER ASS'Y (TPL ROW) V TYP -	
		 0 PLG ±- 1 PLG ±0.5 2 PLG ±0.13 3 PLG ±0.013 4 PLG ±0.0001 ANGLES ±- FINISH - 		SIZE A2	
MATERIAL SEE TABLE		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-179843	
				RESTRICTED TO -	
				SCALE 5:1	
				SHEET 1 OF 1	
				REV C1	