

4

3

2





1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	FIRST ISSUE	01-JUN-06	PW	JB



NOTES:

- PART NUMBER 1857770-1 AS SHOWN.
- MATERIAL:
 - HOUSING: THERMOPLASTIC, HIGH TEMP., UL94V-0; COLOR:BLACK.
 - CONTACTS: PHOSPHOR BRONZE
- FINISH:
 - CONTACT:
 - 30μ" MIN. GOLD PLATING ON CONTACT AREA.
 - 100μ" MIN. TIN PLATING ON SOLDER TAILS,
 - 50μ" MIN. NICKEL UNDERPLATING OVERALL.
- NORMAL FORCE: 80g/PIN MIN. AT 0.65mm DEFLECTION.
- THIS PRODUCT IS ROHS COMPLIANT.
- WORKING AREA: 0.65mm TO FULL COMPRESSION.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P.Willems		01-JUN-06		tyco		Tyco Electronics Corporation	
		CHK E.Stellinga		01-JUN-06		Electronics		s-HertogenBosch,Nederland,	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.Broeksteeg		01-JUN-06		NAME	
		0 PLC ± 0,5		PRODUCT SPEC		SIM CARD CONN. 8P/2P OMITTED WITH 2P SWITCH			
		1 PLC ± 0,3		—					
		2 PLC ± 0,2		APPLICATION SPEC					
		3 PLC ± —		—		SIZE		CAGE CODE	
		4 PLC ± —				DRAWING NO		RESTRICTED TO	
MATERIAL		FINISH		WEIGHT		A3		00779	
—		—		—		C=1857770		—	
CUSTOMER DRAWING						SCALE		SHEET	
						—		1 OF 1	
								REV	
								A	