

1				
REVISIONS				
DESCRIPTION	DATE	DWN	APVD	
CR-18-006945	29MAY2018	NG	MZ	
				D
OTES:				
) FOR ALL POLARISATION	N KEYS			
SEE TABLE ON SHEET 2	2 OF 2			
2 TE LOGO				
<u>L</u> TE LOGO				
RATED VOLTAGE				
<u> </u>				С
4 rated current and c	CABLE SI	ΖE		
) PARTS UNDER APPROVAL				
ACCORDING TO LEC 615 PARTS TO BE TESTED A	ACCORDI	١G		
TO INTERNAL TE ENDUF PROCEDURE	RANCE II	<u>-</u> S I S))	
) PARTS RELEASED FOR F	PRODUCT	ION		
WITH THE EXCEPTION OF COMPONENTS WHICH ARE	E NOT YE	ΞT	ΥL	
RELEASED AND CURREN ⁻ TESTING	ILY UNDE	<u>-</u> R		
ER 5 POS CONN. SEALED . NECTOR M-LINE .	+879999	-5-	В	В
R 5 POS CONN. SEALED IECTOR M-LINE	+879999	-4-	В	
R 5 POS CONN. SEALED	+879999	-3-	В	
IECTOR M-LINE	+879999		В	
IECTOR M-LINE				
IECTOR M-LINE	1879999	-	В	
DESCRIPTION	PART NUMBEI	7	REV.	
STE TE CO	nnectivit	v		
)		
NECTOR M-LINE 5 POLE T-SPLITTER CONNECTOR	S			
SEALED VERSION				A
AGE CODE DRAWING NO		RESTR	ICTED TO	
- C=1879999			-	
scale 2:1	T OF 3	R	^{ev} B	J

	2		3	4	
			R PUBLICATION 2013 RIGHTS RESERVED.		
SEE SHEET I	P LTR				
		SCALE I:I	POLARISATION KEYS		
	-	ТҮРЕ "С-С"	TYPE "B-B"	ТҮРЕ "А-А"	_
F					
		P/N -1879999-3-	P/N 1879999 2 TYPE "E-E"	P/N 1879999-1 TYPE "D-D"	-
			P/N +879999-5	P/N 1879999-4	
			TYPE "E-E"	TYPE "D-D"	

		снк 08MAY20I3 М. ZUCCA		
dimensions: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 08MAY2013 J. CATCHPOLE	NAME	NE
	0 PLC ±- 1 PLC ±0.3 2 PLC ±0.20 3 PLC ±- 4 PLC ±- ANGLES ±3*	PRODUCT SPEC - APPLICATION SPEC -	SIZE	T - S E cage
MATERIAL –	FINISH -	WEIGHT _	A 3	_
-	-	Customer Drawing		


1470-19 (3/13)

D

С

В

А



F	THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2013 (C) COPYRIGHT 2013 BY - ALL RIGHTS RESERVED.			REVISIONS]
		P	L T R -	DESCRIPTION SEE SHEET I	DATE D	WN APVD	-
D							
	N N S2						
	SI SI KEMA SI KEMA SI KEMA SI KEMA SI SI SI SI SI SI SI SI SI SI						
С	PE LI PE ADDITIONAL D						С
_	(S2) (N) CAVITY CIRCU						
В	SI CONSIGNATION CO						В
	PE (LI)						
A	DIMENSIONS: TOLERANCES UNLESS OTHERWISE SPECIFIED: AP MM 0 PLC ±- 1 PLC ±0.3	A 71100	2A 081 2A 081 CHPOL	NECTOR M-LINE 5 POLES T-SPLITTER CONNECTOR	ectivity		
	MATERIAL - AP	PLICATION IGHT ISTOMER	-	SEALED VERSION SIZE CAGE CODE DRAWING NO A 3 - C 1879999 SCALE 2:1 SHEET	RES 3 ^{OF} 3	TRICTED TO	

TE Connectivity	
NECTOR M-LINE 5 POLES T-SPLITTER CONNECTOR SEALED VERSION	A
GE CODE DRAWING NO RESTRICTED TO	
- C-1879999 -	
SCALE 2:1 SHEET 3 OF 3 REVBI	