





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
I		PROPOSAL DRAWING	12MAR2010	IL	SY
A		REV PER ECR-10-005525	18MAR2010	IL	SY
A1		REMOVED NOTE-2	24SEP2024	VNB	RCG



ISOMETRIC VIEW




- ⚠ MATERIAL: THERMO PLASTIC, UL94 V-0.
- Ⓜ ⚠ DELETED
- Ⓜ ⚠ PANEL THICKNESS = .040±.005
- ⚠ CONNECTOR KEEP OUT ZONE.
- Ⓜ ⚠ POWER CONTACT REFERENCE:
PART NUMBER: 1600960 & 1600961
MATERIAL: COPPER ALLOY
FINISH (INTERFACE):.0000030 Au OVER .0000050 Ni



REF: POWER SECONDARY LOCK
PART NUMBER: 1600903-1

POWER POSITION 1



4P	1892981-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN I. LEE 12MAR2010	NAME TE TE Connectivity SLIDE TO LOCK PANEL MOUNT CABLE RECEPTACLE HOUSING, WITH SLIM GUIDES, MULTI-BEAM XLE
DIMENSIONS: INCHES		CHK S. ZHAO 12MAR2010	
		APVD S. YAO 12MAR2010	
		PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO
0 PLC ±.005 1 PLC ±.005 2 PLC ±.005 3 PLC ±.005 4 PLC ±.0020 ANGLES ±2° FINISH		WEIGHT	
MATERIAL		CUSTOMER DRAWING	SCALE 3:1
			SHEET 1 OF 2
			REV A1

