

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20

© COPYRIGHT 20 ALL RIGHTS RESERVED.

CRIMPING DATA (CURRENT STANDARD) (DADOS DE GRAMPEAÇÃO)

Table with columns: LETRA DO DISCO (DISC LETTER), CRIMP HEIGHT (ALTURA DE FECHAMENTO), WIRE SIZE (BITOLA). Rows A, B, C.

WIRE STRIP LENGTH: (COMPRIMENTO DO DECAPE) 3,90-4,70 MM

CRIMPER (GRAMPEADOR), CRIMP WIDTH (LARGURA), TYPE (TIPO), APPLICATOR FEED (PASSO)

WIRE (CONDUTOR), INSULATION (ISOLANTE)


INSULATION RANGE (DIAM. DO ISOLANTE), WIRE RANGE (PARA BITOLAS), GAGE (GABARITO DE MONT.)

TERMINALS APPLIED (PARA APLICAR TERMINAL)

Table with columns: TERMINAL, SEAL (SELO), TERMINAL, SEAL (SELO). Rows (A) 964269, (B) 964274.

PREFERRED STANDARD TO MEET NEW REQUIREMENT LV214-2 SLOW MOTION BENDING TEST

Table with columns: LETRA DO DISCO (DISC LETTER), CRIMP HEIGHT (ALTURA DE FECHAMENTO), WIRE SIZE (BITOLA). Rows A, B, C.



NOTE: 1 - GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN BENCH PRESS. 2 - ONLY THE ITEMS WITH QUANTITY ARE USED ON THIS APPLICATOR.

3 - TO CONVERT THE APPLICATOR TO A NON-CARRIER CUTTING STYLE, REMOVE ITEMS 139 E 140

KEYS: □ - SPARE PARTS RECOMMENDED. ▢ - GREASY LIGHTLY.

NOTAS: 1 - USAR PROTEÇÃO QUANDO FOR USADO EM PRENSA DE BANCADA. 2 - APENAS OS ITENS COM QUANTIDADES ESPECIFICADAS SÃO USADOS NESTE APLICADOR. 3 - PARA "NÃO" CORTAR A FITA DO CARRIER, REMOVA OS ITENS 139 E 140.

RECOMENDAÇÕES: □ - PEÇAS DE DESGASTE O CLIENTE SERÁ RESPONSÁVEL PELA REPOSIÇÃO. ▢ - ENGRAXAR LEVEMENTE.

Table with columns: PART NUMBER (NÚMERO), DESCRIPTION (DESCRIÇÃO). Rows for KIT DE APLICAÇÃO and APPLICADOR MINI PNEUMÁTICO.

Large parts list table with columns: QTY PER ASS'Y, PART NUMBER, DESCRIPTION, ITEM. Includes a revision table at the top right.

Technical drawing header and footer containing dimensions, tolerances, material, and customer information.