

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DS	-		A	RELEASE	08. AUG. '08	GC	JK



ISO VIEW

TABLE 1. APPLICABLE TAB CONTACT.


TAB	PART NO.	WIRE RANGE	
		mm ²	INSULATION DIA. (FLK)
MCP 9.5mm	963766	4.0-6.0	2.4-5.2
	963768	6.0-10.0	4.7-6.6

NOTE ;

1. GENERAL TOLERANCE : ± 0.3 , $\pm 3.0^\circ$
2. APPLICABLE TAB CONTACT : SEE TABLE 1.
3. THE MATING PLUG ASS'Y P/N : 936619

TABLE 2. MCP 9.5mm CAP HSG KEY CODE

0-1897198-2	1-1897198-1	2-1897198-3
3-1897198-4	4-1897198-7	5-1897198-8



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm .5$
1 PLC $\pm .5$
2 PLC ± 0.13
3 PLC ± 0.013
4 PLC ± 0.0001
ANGLES $\pm$

FINISH

MATERIAL

DWN
GC KWON
CHK
KT LIM
APVD
JK SONG
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

08AUG2008
-
-
-
-
-

CUSTOMER DRAWING

AMP KOREA
kyungsan. korea

NAME
MCP 9.5 2P CAP HSG

SIZE
A300779

CAGE CODE
C-1897198

DRAWING NO

RESTRICTED TO

SCALE

SHEET

OF

REV
A