



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
DS	-		A	RELEASE	22. JAN. '08	GC	JK
			B	REVISED(ECR-08-032199)	21. APR. '08	GC	JK



ISO VIEW

TABLE 1. APPLICABLE TAB CONTACT.

TAB	PART NO.	WIRE RANGE	
		AWG	mm ²
040	353537-1	22-20	0.3-0.5
090	368088-1	22-20	0.3-0.5
	368087-1	18-16	0.85-1.25
	368086-1	14	2.0

NOTE ;

1. GENERAL TOLERANCE : ± 0.3 , $\pm 3.0^{\circ}$
 2. APPLICABLE PANEL SIZE : SEE FIG. 1
 3. APPLICABLE PANEL THICKNESS : 0.7 mm
 4. APPLICABLE TAB CONTACT : SEE TABLE 1.
 5. THE MATING PLUG ASS'Y P/N : 1897228
 6. THE MATING COVER P/N : 1897227(AM)
- △ DBL SUPPLY CONDITION : 1ST LOCKING.






Fig. 1 APPLICABLE PANEL SIZE

3	1897226-2	PANEL SEAL	EPDM	BLACK	I
2	1897225-1	CAP DBL	PBT	WHITE	I
1	1897224-2	CAP HSG	PBT	BLACK	I
NO.	PART NO.	DESCRIPTION	MATERIAL	COLOR	Q'TY

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN GC KWON 21APR2008		Tyco Electronics kyungsan, korea	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
0 PLC ±0.5 1 PLC ±0.13 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±		APVD KT LIM		CAP HSG ASS'Y FOR HYB(040/090) DOOR 30P	
MATERIAL -		FINISH -		PRODUCT SPEC -	
		APPLICATION SPEC -		WEIGHT -	
		CUSTOMER DRAWING		RESTRICTED TO -	
		SCALE 1:1		SHEET 1 OF 1	
		REV B			