

LOC	DIST	REVISIONS					
J							
		F	LYR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	10DEC08	KK	HY
			A1	REVISED ECR-12-000796	13JAN12	KF	HY
			A2	REVISED ECR-09-014331	13SEP12	KK	HY

-1,-7;本図
-1,-7;AS SHOWN








TABLE-1

		APPLIED TERMINAL P/N 適用端子 P/N	APPLICABLE WIRE RANGE 適用電線
SIGNAL 0.5	TIN	1827855-4	0.13~0.5mm ²
	TIN	1827855-1	
	GOLD	1903703-1	
	TIN	1827855-2	
	TIN	1827855-3	

1. 本製品は、別番のコンポーネントと組合せて使用する。
2. 取扱説明書：NO:411-78268
3. 組合せ相手型番：取扱説明書を参照のこと。
4. 嵌合相手代表型番：取扱説明書を参照のこと。
5. 適用端子：TABLE-1参照

1. THIS PRODUCT IS USED STACK WITH ANOTHER COMPONENTS.
2. HANDLING OF THIS PART SHOULD FOLLOW INSTRUCTION SHEET NO.411-78268.
3. COMPONENTS NUMBER OF STACKING;REFERENCE TO INSTRUCTION SHEET.
4. MATING CONNECTOR PART(TYPICAL);REFERENCE TO INSTRUCTION SHEET.
5. APPLIED TERMINAL:SEE TABLE-1

PAPER BOX ダンボール箱	SOFT TRAY プラスチックトレイ	GRAY	1903994-7
		NATURAL	1903994-3
			1903994-2
			1903994-1
OUTER 外装	INNER 内装	COLOR	PART NO.
PACKING STYLE 梱包形態			

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN A.KATO	10DEC08	TE TE Connectivity		
DIMENSIONS: 単位: ㎜			CHK R.KOMIYAMA	10DEC08			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 単位: ㎜			APVD H.YAMAGAMI	10DEC08	NAME 0.5 6 POSITION LOCK HOUSING STACKING TYPE	
	-0.20 ± 0.3			PRODUCT SPEC			
	+0.10 -0.1			108-78437			
	+0.10 -0.5			APPLICATION SPEC			
	+0.10 -0.13			R010000000			
	+0.10 -0.090						
MATERIAL 材料	ANGLES 45°/90°			SIZE		RESTRICTED TO	
	FINISH 仕上			CASE CODE			
	PBT			DRAWING NO			
				A100779C1903994			
			WEIGHT		SHEET		
			CUSTOMER DRAWING		5:1		
					OF		
					REV A2		