

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

SEP ,2010.

© COPYRIGHT 2010 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

變更

DESCRIPTION

DATE

DWN

APVD

ES

—

P

LTR

A

RELEASE

11JUN2011

F.C

S.Y

1 CONTACT COPLANALITY IS 0.1 MAX.

2 THIS DIMENSION MEANS CENTER OF THE POCKET.

3 M3 TAPPING + BVTP RECOMMENDED TORQUE: 68.6N (7Kgf) MAX.

4 FINISH

CONTACT: V μm MIN. Au PL. ON CONTACT AREA (V: SEE TABLE)

0.03~0.1 μm Au PL. ON TERMINAL AREA

Ni UNDER PL. ALL OVER

SHELL: Sn PL. (MATTE) ALL OVER

Ni UNDER PL. ALL OVER

5 SCREW SIZE

0.1	—	400	1.9	WITHOUT TAPE	WITHOUT FLANGE	THROUGH HOLE	(SEE SHEET 2)	(SEE SHEET 4)	1932754-2
0.1	—	70	1.9	WITHOUT TAPE	WITHOUT FLANGE	THROUGH HOLE	(SEE SHEET 2)	(SEE SHEET 3)	1932754-1
V	U	—	AA	POLYIMIDE TAPE	FLANGE	SHELL TYPE	CONNECTOR	PACKAGE	PART NUMBER
4Au PL.	5SCREW SIZE	QTY	DIM.	PART LIST					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
單位：耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH
仕上

MATERIAL
材料

DWN
C.FISHER
3SEP2010

CHK
L.MARTIN
3SEP2010

APVD
Y.STEVEN
3SEP2010

PRODUCT SPEC
製品規格
108-78180-2

APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

TE Connectivity

HDMI 19 POS RECEPTACLE ASSY
SMT SHORT TYPE

SIZE
A3

CAGE CODE
00779

DRAWING NO
番号
C-1932754


RESTRICTED TO
—


SCALE
尺度
4:1

SHEET
1 OF 5




REV
A

1470-19 (3/11)







SECTION E-E



SECTION D-D




SECTION C-C



DETAIL A
SCALE 5:1

NOTE FOR THIS PAGE:

1.MATERIAL:PS 0.8mm±0.05, COLOR:NATURAL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity			
		CHK					
DIMENSIONS: 単位： 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称		HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE	
		0 PLC ± 0.5		PRODUCT SPEC 製品規格			
		1 PLC ± 0.5		APPLICATION SPEC 取付適用規格			
2 PLC ± 0.5							
3 PLC ± 0.5		WEIGHT		SIZE		CAGE CODE	
4 PLC ± 0.5				A3		00779	
ANGLES ± 2°				DRAWING NO 番号		C-1932754	
MATERIAL 材料		FINISH 仕上		RESTRICTED TO		—	
				CUSTOMER DRAWING		SCALE 尺度 4:1	
						SHEET 3 OF 5	
						REV A	



4

3

2


1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
ES			-	SEE SHEET 1	-	-





SECTION A-A


- NOTES FOR THIS PAGE:
- 1.QUANTITY 350PCS/REEL.
 - 2.REELING DIRECTION IN DELIVERY




- 3.USER DIRECTION OF FEED



SECTION B-B





- 4.COVER TOVER TAPE PEELING FORCE




PEELING SPEED 300mm/Min.(REF.)

A	170°~180°
F	0.1N~1.3N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity			
		CHK				
		APVD				
DIMENSIONS: 単位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称		
		0 PLC	± 0.1	HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE		
		1 PLC	± 0.1			
		2 PLC	± 0.1	PRODUCT SPEC 製品規格		
		3 PLC	± 0.1			
		4 PLC	± 0.1	APPLICATION SPEC 取付適用規格		
		ANGLES	± 2°			
MATERIAL 材料		FINISH 仕上		SIZE	CAGE CODE	DRAWING NO 番号
				A3	00779	C-1932754
CUSTOMER DRAWING				WEIGHT	RESTRICTED TO	
				SCALE 尺度 4:1	SHEET 4 OF 5	REV A



MATING CONDITION (REFERENCE)
(SCALE 2:1)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		TE Connectivity				
		CHK						
DIMENSIONS: 単位： 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称				
		APVD		HDMI 19 POS RECEPTACLE ASSY SMT SHORT TYPE				
		PRODUCT SPEC 製品規格						
		APPLICATION SPEC 取付適用規格						
		WEIGHT						
MATERIAL 材料		FINISH 仕上		SIZE		CAGE CODE	DRAWING NO 番号	RESTRICTED TO
				A3		00779	C-1932754	—
CUSTOMER DRAWING				SCALE 尺度		SHEET		REV
				4:1		5 of 5		A