













LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
J				SEE SHEET 1 OF 2		




26POS(X-KEY): I-1939638-3

28POS(X-KEY): I-1939638-4

30POS(X-KEY): I-1939638-5

40POS(X-KEY): I-1939638-0

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. MAEBASHI 30JUL2007		TE Connectivity			
		CHK T. KUDO 30JUL2007					
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME DYNAMIC D1100D 2.0mmPITCH HDR ASSY, H-TYPE 22-40POS			
		0 PLC ±- 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±-					
MATERIAL -		FINISH -		SIZE A300779 CAGE CODE C-1939638 DRAWING NO RESTRICTED TO -			
Customer Drawing				SCALE 2:1		SHEET 2 OF 2	REV C4