

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006  
 © COPYRIGHT 2006 BY TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS  
変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECR-10-007266	22APR2010	HMR	T.M
C		REVISED PER ECR-14-001037	24JAN2014	K.T	N.Y
D		REVISED PER ECR-16-015895	20NOV2016	K.T	E.T

1. MATERIAL: HOUSING: LIQUID CRYSTAL POLYMER  
 COLOR: BLACK  
 CONTACT: COPPER ALLOY  
 SOLDER PEG: BRASS

2. FINISH (ALL OVER): NICKEL PLATING 1.27μm MIN

3. FINISH (CONTACT AREA): GOLD PLATING 0.76μm MIN AFTER 2

4. FINISH (SOLDER PEG & CONTACT TAIL): TIN PLATING 2μm MIN AFTER 2

5. COPLANARITY 0.15mm MAX. (CONTACT TINE AND SOLDER PEG ONLY)

6. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

7. THE KEYING ARRANGEMENT OF "Y" IS SYMMETRIC WITH "X".

1. 材料: ハウジング: 液晶ポリマー、色: 黒  
 コンタクト: 銅合金  
 ソルダーペグ: 黄銅

2. めっき(全面): ニッケル下地めっき 1.27μm 以上

3. めっき(接触部): 2の上 に金めっき 0.76μm 以上

4. めっき(ソルダーペグとコンタクト半田付部): 2の上 に錫めっき 2μm 以上

5. コンタクトタイン部及びソルダーペグの平面度(コプラナリティ)は 0.15mm MAX

6. 文字の形状、大きさ、および位置等は、大略を示すものであり詳細を示すものではありません。

7. Y KEY形状は、X KEY形状と左右対称

SCALE 1:1

OUTLINE OF HDR HSG

REFERENCE PC BOARD PATTERN: CONNECTOR MOUNT SIDE (NOT ACCUMULATE TOLERANCE)  
 参考基板取付寸法: コネクタ搭載面 (非累積公差)

DETAIL A SCALE 4:1  
 DETAIL B SCALE 4:1

	0.76μm MIN	40	Y	19	38.0	43.2	48.6	48.44	21.6	2-1939995-0
	0.76μm MIN	40	X	19	38.0	43.2	48.6	48.44	21.6	1-1939995-0
	0.76μm MIN	26	Y	12	24.0	29.2	34.6	34.44	14.6	2-1939995-3
	0.76μm MIN	26	X	12	24.0	29.2	34.6	34.44	14.6	1-1939995-3
OBSOLETE	0.38μm MIN	22	X	10	20.0	25.2	30.6	30.44	12.6	1-1939995-4
	GOLD	POS	KEY	n	A	B	C	D	E	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN M. MAEBASHI 06NOV2006  
 CHK T. KUDO 06NOV2006  
 APVD D. MITSUGI 06NOV2006

NAME 名称 DYNAMIC D1100D 2.0mm PITCH HDR ASSY, SMT/V-TYPE 22-40POS

PRODUCT SPEC 108-78414  
 APPLICATION SPEC 114-5405

WEIGHT  
 Customer Drawing

SIZE A3 CAGE CODE 00779 DRAWING NO. 1939995 RESTRICTED TO

SCALE 尺度 2:1 SHEET 1 OF 2 REV D

1470-19 (3/13)

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2006

© COPYRIGHT 2006 BY -

ALL RIGHTS RESERVED.

REVISIONS

変更

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

Dimensions: C, B,  $2Xn=A$ , D REF (PEG)

26POS(X-KEY): 1-1939995-3

Labels: 13, 1, D1100

Dimension: E

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
単位: 耗  
mm

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

一般公差	±
0 PLC	±0.5
1 PLC	±0.13
2 PLC	±0.013
3 PLC	±0.001
4 PLC	±0.0001
ANGLES	±

MATERIAL  
材料  
TBDFINISH  
仕上

DWN 06NOV2006

M. MAEBASHI

CHK 06NOV2006

T. KUDO

APVD 06NOV2006

D. MITSUGI

PRODUCT SPEC

108-78414

APPLICATION SPEC

114-5405

WEIGHT

Customer Drawing

TE Connectivity

NAME  
名称DYNAMIC D1100D 2.0mmPITCH  
HDR ASSY, SMT/V-TYPE  
22-40POS

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1939995

RESTRICTED TO

-

SCALE  
尺度

2:1

SHEET

2 OF 2

REV

D

1470-19 (3/13)