


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		C	REV PER ECO-15-017559	05JAN16	KG	PD



- 1 WIRE INSULATION: .500-.574 DIA
- 2 THE TONGUE RADIUS FEATURE IS NOT A TOOLING CONTROLLED DIMENSION AND MAY NOT BE A TRUE RADIUS.
- 3 STAMP "AMP 2/0 AL N"
SIZE AND LOCATION APPROX AS SHOWN



INSERT & FUNNEL: BRASS MIL-C-50
NICKEL PL QQ-N-290 .000300 AVG THK

BODY: COPPER ASTM-B187 ANNEALED
NICKEL PL .000300 MIN THK PER QQ-N-290

1958060-1

MATERIAL & FINISH

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	05JAN07	 TE Connectivity					
DIMENSIONS: INCHES		CHK JOHN KNOLL	05JAN07						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JOHN KNOLL	05JAN07	NAME WIRE TERMINAL, RING TONGUE, SEALED COPALUM, BENT 15, WIRE SIZE: 2/0 ALUMINUM				
			PRODUCT SPEC —						
			APPLICATION SPEC —						
	MATERIAL	FINISH		WEIGHT	81 GRAMS	SIZE A2	CAGE CODE 00779	DRAWING NO C=1958060	RESTRICTED TO —
SEE TABLE	SEE TABLE		CUSTOMER DRAWING				SCALE 2:1	SHEET 1 of 1	REV C