





INSERT & FUNNEL: BRASS MIL-C-50 NICKEL PL .000300 MIN THK PER QQ-N-290	1958093-1
BODY: COPPER ASTM-B187 ANNEALED NICKEL PL .000300 MIN THK PER QQ-N-290	
MATERIAL & FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 23FEB07	TE Connectivity				
DIMENSIONS: INCHES		CHK J KNOLL 23FEB07					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J KNOLL 23FEB07	NAME WIRE TERMINAL, RING TONGUE, SEALED COPALUM, HIGH TEMP, BENT 15, WIRE SIZE: 3/0 ALUMINUM			
			PRODUCT SPEC —				
			APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C=1958093	RESTRICTED TO —
	MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT 103±5 g				
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV E		