


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER ECO-10-025932	21DEC10	HMR	DR

AMP
WIRE RANGE

16-14 AWG
SOLID OR STRANDED



- 1
- STAMP AMP 16-14* APPROX AS SHOWN

2

3

4

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62mm ² [2,050-5,180] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	

10,000		LOOSE PIECE	1958371-1
QTY	PACKAGE TYPE		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 04NOV09	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: MM [in] [INCHES]		CHK DAN ROHDE 04NOV09		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		SPLICE, BUTT, W/SIGHT HOLE SOLISTRAND, 16-14, ANNEALED	
	FINISH		RESTRICTED TO	
MATERIAL	3	4	SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING		WEIGHT -	DRAWING NO C=1958371	REV A
		SCALE 10:1	SHEET 1 OF 1	