





LOC		DIST		REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		B		REVISED PER ECO-10-001317	25JAN2010	DH	JE	



SCALE 4.000

- NOTES:
- UNLESS OTHERWISE SPECIFIED
- 1 MATERIAL: 6063 ALUMIMUM.
- 2 FINISH: ELECTROLESS NICKEL 0.76-2.54µm THICK
RoHS COMPLIANT.
3. 0.2mm MAX BURR.
4. VARIATION IN PLATING COLOR IS NORMAL AND ALLOWED.
- 5 MAXIMUM PIN LEAN OF 8° IN ANY DIRECTION.
6. RoHS COMPLIANT AND CERTIFIED.

2	SALE PART	1963784-2
NOTES	DESCRIPTION	PART NUMBER

DWN D. HUMBERT 25JAN2010 CHK J. EABY 25JAN2010 APVD J. EABY 25JAN2010		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm		NAME OSFP DOUBLE LAN HEATSINK 13.5mm TALL	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±.25 1 PLC ±0.13 2 PLC ±0.051 3 PLC ±.1 4 PLC ±.1 ANGLES ±1°		RESTRICTED TO -	
MATERIAL SEE NOTE #1		WEIGHT -	
FINISH SEE NOTE #2		CUSTOMER DRAWING	
SCALE 6.000		SHEET 1 OF 1	
REV B			