

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-24-213594	01JUL2024	RK	FJS

D

C

B



A

D

C

B

A



RECOMMENDED PC BOARD LAYOUT

- 1 HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED
- 2 CONTACT MATERIAL: BRASS PER ASTM B36
- 3 0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81µm [.000150] MIN LEAD FREE TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.GRZYBOWSKI 9JUNE09	TE Connectivity		1986567-1 PART NO	
DIMENSIONS: mm [INCHES]		CHK G.STEINHAUER 9JUNE09				
		APVD M.PERCHERKE 9JUNE09	NAME PIN HEADER ASSEMBLY, 9 POSITION, METRIMATE		SIZE CAGE CODE DRAWING NO A2 00779 C=1986567	
		PRODUCT SPEC 108-10033				
MATERIAL HOUSING: 1 CONTACT: 2		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC -		RESTRICTED TO -	
FINISH CONTACT: 3		WEIGHT -	CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
					REV C	

1986567