




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECR-24-213594	01JUL2024	RK	FJS

- ① HOUSING MATERIAL: PA66, BLACK, UL 94 V-0 RATED.
- ② CONTACT MATERIAL: BRASS PER ASTM B36.
- ③ 0.76µm [.000030] MIN PRECIOUS METAL PLATE FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81µm [.000150] MIN LEAD FREE TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27µm [.000050] MIN NICKEL.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.GRZYBOWSKI 9JUNE09	TE Connectivity	
		CHK G.STEINHAUER 9JUNE09		
DIMENSIONS: mm [INCHES]		APVD M.PERCHERKE 9JUNE09	NAME PIN HEADER ASSEMBLY, 12 POSITION, METRIMATE	
		PRODUCT SPEC 108-10033	SIZE A2	
		APPLICATION SPEC		
MATERIAL ① ② ③		WEIGHT -	CAGE CODE 00779	DRAWING NO C=1986569
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH ③		CUSTOMER DRAWING		RESTRICTED TO -
		SCALE 4:1	SHEET 1 OF 1	REV C