

4

3

2

1



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	28JAN2015	NV	PS
	A1	P/N 1986818-4 ADDED IN TABLE	22SEP2016	FP	NG

NOTES:

1. MATERIALS & FINISH
HOUSING : PA , UL94 V0, COLOR - BLACK
PIN : COPPER ALLOY, TIN PLATED
2. MECHANICAL
INSERTION FORCE PER POLE :2.5N
WITHDRAWAL FORCE PER POLE:4.5N
3. ELECTRICAL
VOLTAGE RATING : 300 V [UL,USAGE GROUP B.D]
CURRENT RATING : 15 A [DEPEND UPON PLUG]
CONTACT RESISTANCE : < 15 m Ohm
INSULATION RESISTANCE : > 1000 M Ohm (500V DC)

4. OPERATING TEMPERATURE BETWEEN -40 °C TO +110 °C

△ 5 TOLERANCE NOT CUMULATIVE



-3 AS SHOWN

4	1986818-4
3	1986818-3
NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28JAN2015 NAGASHREE.V	TE Connectivity		
		CHK 28JAN2015 PRASHANTH.S			
		APVD 28JAN2015 PRASHANTH.S	NAME TERMINAL BLOCK HEADER, ORTHOGONAL RITCH 5mm,RIGHT VERSION		
DIMENSIONS: mm		PRODUCT SPEC			
		APPLICATION SPEC			
		WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO C-1986818
MATERIAL SEE NOTE 1		FINISH SEE NOTE 1	RESTRICTED TO -		
			Customer Drawing		
			SCALE 3:1	SHEET 1 OF 1	REV A1